


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0436450800](#)
Status: **Active**
Overview: [Micro-Fit 3.0 Connector System Product Family](#)
Description: [Micro-Fit 3.0 Receptacle Housing, Single Row, 8 Circuits, UL 94V-0, Black](#)

Documents:

Drawing (PDF)	Product Specification TS-46235-001-001 (PDF)
3D Model	Application Specification 430250000-AS-000 (PDF)
Product Specification PS-43650 (PDF)	Packaging Specification PK-43645-001-001 (PDF)
Product Specification TS-43045-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-43045-002-001 (PDF)	Product Literature (PDF)



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	43645
Application	Power, Wire-to-Wire
Overview	Micro-Fit 3.0 Connector System Product Family
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0
UPC	800753944329

Physical

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.004/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	430250000-AS-000
Packaging Specification	PK-43645-001-001
Product Specification	PS-43650, TS-43045-001-001, TS-43045-002-001, TS-46235-001-001
Sales Drawing	436450000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43645 Series](#)

Mates With

Micro-Fit 3.0 Plug Housings [43640](#)

Micro-Fit* TPA Plug Housing [200875](#)

Micro-Fit 3.0 Headers [43650](#)

Use With

Micro-Fit 3.0 Female Crimp Terminals [43030](#), [45773](#), Micro-Fit RMF Female Crimp Terminals [46235](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION