


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5018648090**  
**Status:** **Active**  
**Overview:** FFC-FPC (SMT)  
**Description:** 0.50mm Pitch Easy-On FFC-to-Board Connector, Receptacle Housing Assembly, Right-Angle, Surface Mount, without Grounding Terminals, Gold (Au) Plating, 80 Circuits

**Documents:**

[3D Model](#) [Packaging Specification SPK-501864-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-501864-001-001 \(PDF\)](#)



**Agency Certification**

UL E29179

**General**

Product Family FFC/FPC Connectors  
 Series 501864  
 Comments Requires a custom FFC with notches  
 Overview FFC-FPC (SMT)  
 Product Name Easy-On  
 UPC 822350206426

**Physical**

Actuator Type FFC-to-Board  
 Circuits (Loaded) 80  
 Circuits (maximum) 80  
 Color - Resin Black  
 Contact Position Bottom  
 Durability (mating cycles max) 20  
 Flammability 94V-0  
 Mated Height 4.85mm  
 Material - Metal Copper Alloy  
 Material - Plating Mating Gold  
 Material - Plating Termination Gold  
 Material - Resin Liquid Crystal Polymer  
 Net Weight 903.840/mg  
 Number of Rows 1  
 Orientation Right Angle  
 PCB Locator Yes  
 PCB Mounting Surface Mount  
 PCB Retention Yes  
 Packaging Type Embossed Tape on Reel  
 Pitch - Mating Interface 0.50mm  
 Polarized to PCB Yes  
 Stackable No  
 Temperature Range - Operating -40° to +105°C  
 Wire/Cable Type FFC only

**Electrical**

Current - Maximum per Contact 0.5A  
 Voltage - Maximum 50V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification SPK-501864-001-001  
 Product Specification PS-501864-001-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/61/2018 (27 June  
 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

501864 Series

**Use With**

Plug Jacket 501783-8009 . Plug Jacket  
 Cover 501784-8009 <br>LVDS Cable 15022

This document was generated on 10/11/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**