

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0533980671](#)
Status: **Active**
Overview: [PicoBlade Connector System](#)
Description: 1.25mm Pitch PicoBlade Header, Surface Mount, Vertical, 6 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-53398-002-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51021-024-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Headers
 Series [53398](#)
 Application Signal, Wire-to-Board
 Current Derating Order No 987651-3691
 Overview [PicoBlade Connector System](#)
 Product Name PicoBlade
 UPC 822348164332


Physical

Breakaway No
 Circuits (Loaded) 6
 Circuits (maximum) 6
 Color - Resin Natural
 Durability (mating cycles max) 30
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Capable No
 Guide to Mating Part No
 Lock to Mating Part Yes
 Mated Height 5.70mm
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 214.700/mg
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 0.60mm
 PCB Locator No
 PCB Retention Yes
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 1.25mm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Shrouded Partial
 Stackable No
 Temperature Range - Operating -40° to +85°C
 Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 1.0A
 Voltage - Maximum 125V

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[53398 Series](#)

Mates With

PicoBlade Housing [51021](#)
PicoBlade
 Cable Assembly [15134](#)

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

SPK-53398-002-001

PS-51021-024-001

SD-53398-032, SD-53398-033-001

This document was generated on 10/09/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION