

**ToughArmor****MB508SP-B**
**ICY DOCK®**  
[www.icydock.com](http://www.icydock.com)

8 Bay 2.5" HDD/SSD SAS/SATA Hot-Swap  
mobile rack for 2 x external 5.25" bay



**Fits 2x  
5.25" Bay**

**SUPPORTS**

**15pin SATA Power Cable  
with locking latch**



**Mini-SAS HD Connector  
with locking latch  
(SFF-8643)**



Compatible with wide range of PC Chassis



**Support 5-15mm 2.5" Drive Height**  
compatible with high capacity SATA & SAS drives

**80mm Cooling Fan Control****ToughArmor MB508SP-B Features & Specs**

- \*Removable drive tray system for easy maintenance
- \*Rugged heavy duty full-metal construction of all internal and external components - Perfect for rugged and industrial applications that must meet flammability requirements
- \*Fits 8x 5-15mm 2.5" SATA/SAS hard drives or SSDs in 2x 5.25" external CD/DVD drive bays
- \*Large 80mm cooling fan with high, low, and off settings for full control
- \*The cooling fan is replaceable for maximum expandability
- \*Uses 2x Mini-SAS HD port for all 8 drives
- \*All 8 drives powered by 2x SATA 15-pin power cables
- \*LED status lights give you drive updates at a glance
- \*Optional drive ID labels to maintain order when using RAID
- \*Anti-Vibration Technology (AVT) - Creates a safe environment for HDD & SSD
- \*Active Power Technology (APT) - individual LED & cooling fan only powers up if there is a drive installed in the bay
- \*Supports enterprise SAS drives including seagate Exos, HGST Ultrastar C series, Dell, HPE and Toshiba SAS drives
- \*Supports SAS & SATA 6Gbps and hot swap

Model Number	MB508SP-B
Color	Black
Host Interface	2 x miniSAS HD (SFF-8643)
Drive Fit	8 x 2.5" SAS/SATA SSD & HDD
Compatible 2.5" Drive Heights	5mm - 15mm
Device Fit	2 x external 5.25" bay
Transfer Rate	Up to 6 Gb/sec. (depending on hard drive speed)
Power Input	2 x 15pin SATA power port
Insert & Extract connection Via	Direct SATA hard drive connection
Structure	Full metal
Drive Cooling	80mm rear cooling fan / Metal heat dispersion
Power Indicator	Solid green LED
HDD Access Indicator	Flashing green LED
Dimension (L x W x H)	157.9 x 146 x 84mm
Weight	1460g
Package Contents	Device, user manual, drive ID plugs and screws