

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0194320001**
Status: **Active**
Overview: MX150L Industrial Sealed Connector System
Description: MX150L 4 Circuit Female Receptacle for 10-12 AWG Wire, Black

Documents:

3D Model	Packaging Specification PK-19432-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19432-001-001 (PDF)	Product Literature (PDF)

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Crimp Housings
Series	<u>19432</u>
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Yellow, Polarized to Mating Part. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector S
Overview	<u>MX150L Industrial Sealed Connector System</u>
Product Literature Order No	987650-2181
Product Name	MX150L
UPC	822350191524

Physical

Circuits (maximum)	4
Circuits Detail	2x2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Net Weight	19.598/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	30.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19432-001
Product Specification	PS-19432-001-001
Sales Drawing	SD-19432-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/01/2018 (15 January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Prop65

RoHS Phthalates

Green Image

Not Relevant

Compliant

Not Contained

Search Parts in this Series

19432 Series

Mates With

19433-0001 Male Plug

Use With

19434 Female Terminals

This document was generated on 09/11/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION