

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0734154680](#)  
**Status:** **Active**  
**Overview:** [SSMCX Coaxial RF Connectors](#)  
**Description:** 50 Ohms, SSMCX Plug for 1.37mm Micro Coaxial Cable, Bag

**Documents:**

[3D Model](#) [Packaging Specification SD-73415-468-PKG \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 895420100-000 \(PDF\)](#)

**General**

Product Family [RF/Coax Connectors](#)  
Series [73415](#)  
Overview [SSMCX Coaxial RF Connectors](#)  
Product Name [SSMCX](#)  
Style [Cable](#)  
Type [Ultra-microminiature](#)  
UPC [822348430819](#)  
Wire/Cable Type [1.37mm max.](#)

**Physical**

Gender [Plug](#)  
Keying to Mating Part [None](#)  
Net Weight [0.112/g](#)  
Orientation [Straight](#)  
PCB Mounting [N/A](#)  
Packaging Type [Bag](#)  
Panel Mount [No](#)  
Panel Mount Method [N/A](#)  
Reverse Polar [No](#)

**Electrical**

Frequency [6 GHz](#)  
Impedance [50Ω](#)

**Solder Process Data**

Lead-freeProcess Capability [N/A](#)

**Material Info**

**Reference - Drawing Numbers**

[Packaging Specification](#) [895420100-000, SD-73415-468-PKG](#)  
[Sales Drawing](#) [SD-73415-468-001](#)



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Prop65

PropRisk

PropRisk

PropRisk

PropSub

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Missing Compliance  
Data

Cancer

Developmental toxicity

Reproductive toxicity

Lead and its  
compounds

Not Contained

**Search Parts in this Series**

[73415 Series](#)