


Evofire 70mm cut-out IP65 Fire Rated Downlight with Insulation Guard and GU10 holder

Partcode: ILDLFR70D003 / Page: 1



The Evofire Fire Rated Downlight is a safe and attractive fitting for a GU10 LED lamp. The fully open design of the Evofire does not conceal your lamp in a large metal canister, which can trap some of the heat it generates, lowering lamp lifetime and performance. Lamps installed in an Evofire run at up to 10 degrees C cooler than a typical can-style fire rated downlight from leading LED brands - this can extend the lifetime of your lamps.

As well being very tough thanks to its steel construction, The Evofire is also a highly aesthetic choice for Fire Rated lighting. The 1mm blend-in bezel is up to 10 times thinner than typical IP65 rated downlights, has a high quality powder coating and fits almost flush with your ceiling, so the downlight looks discreet and pleasing in any setting.

Featuring a built-in Insulation Guard which allows loft insulation to be safely laid on top of the downlight, while maintaining air-flow around the lamp.

This downlight is fire rated to 30, 60 and 90 minutes in compliance with BS476 Part 21:1987, Air Tightness compliant with Part C and Part L and Resistance to Sound compliant with Part E. See installation guide for full details.

[Watch Video](#)

Evofire shown with Real Colour GU10 LED lamp (sold separately).

Product Details

Partcode: ILDLFR70D003

Check Code: 136192

Range Name: EVOFIRE

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: Fire Rated

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Product Finish: Matt white

Material: Steel, Glass

Construction: Pressed Steel, Glass

Partcode: ILDLFR70D003 / Page: 2

Physical Data

Length: 83mm

Diameter: 85mm

Weight (Unpackaged Single Unit): 100g

Cut Out Diameter: 70mm

Lamp or Luminaire Shape: Round

Luminaire Fixing: Recess mounted

Fire Rating: 30, 60, 90

Electrical Data

Partcode: ILDLFR70D003 / Page: 3

Environmental

IP (Ingress Protection) Rating: IP65

IP Rating (Back/Recessed side): IP20

Packaging



EAN Barcode (unit of 1): 5055788228448

Packaged Weight (Unit of 1): 210g

Length (unit of 1): 90mm

Width (unit of 1): 90mm

Depth (unit of 1): 115mm

Outer packaging info available on website

Product data last updated on: Thursday, October 25, 2018 - 15:59