


2700

SERVICE SET NETWORK NETWORK

The set with all essential tools for the assembly and maintenance of networks in an elegant and handy black case with zip fastener.

23 pcs. tool set consisting of:

No.	Description of individual tools	No.	Description of individual tools
2701	Tool case with middle wall, with a total of 23 pockets and a document compartment.	4-534	Cross-recess screwdriver, as above, blade length 100 mm, size PH 2
2-601	IC-tweezers, nickel plated, 125 mm, for gripping, inserting and removing IC's	4-775	Plastic spring handle for socket wrench
3-603-15	Side cutters with slim, pointed head and special flat cutting edge, semi flush, bicoloured hand guard, dissipative	5-161	Clamping scissors, 130 mm, stainless, with serrated gripping jaws
3-235-16	Telephone pliers with wire cutter, 160 mm, chrome plated, with bicoloured hand guard	5-0601	Rotary stripping tool for 3-stage stripping of coaxial cables Types: RG 58, RG 59 and RG 62
3-815-16	Wire strippers, 155 mm, with adjusting screw for all wire thicknesses, chrome-plated, with bicoloured hand guard	6-203	Socket wrench, chrome vanadium, nickel plated, size 6.0 mm
3-0605	Combination-Crimping Pliers for connector types 6P/6C, 6P/4C, 6P/2C, 8P/8C	6-205	Socket wrench, chrome vanadium, nickel plated, size 8.0 mm
3-0611	Crimping pliers for BNC and TNC coaxial connectors	6-207	Socket wrench, chrome vanadium, nickel plated, size 10.0 mm
4-504	Slotted screwdriver with multi-component handle, blade made from chrome vanadium, chrome-plated, with black tip, 100 x 5.5 mm	6-772	Adjustable wrench, chrome vanadium, 150 mm, jaw opening 0 - 19 mm
4-522	Slotted screwdriver with multi-component handle, blade made from chrome vanadium, chrome-plated, with black tip, 75 x 3.0 mm	6-985 L	TORX screwdriver with multi-component handle, blade of chrome-vanadium, chrome-plated, with black tip, size T 10, with bore hole in the tip
4-532	Cross-recess screwdriver with multi-component handle, blade of chrome-vanadium, chrome-plated, with black tip, blade length 60mm, size PH 0	6-986 L	TORX screwdriver with multi-component handle, blade of chrome-vanadium, chrome-plated, with black tip, size T 15, with bore hole in the tip
4-533	Cross-recess screwdriver, as above, blade length 80 mm, size PH 1	6-987 L	TORX screwdriver with multi-component handle, blade of chrome-vanadium, chrome-plated, with black tip, size T 20, with bore hole in the tip
		8-390	Desoldering pump, 195 mm long, Ø 20 mm
		8-376	Gas soldering iron „PIEZO INDY 75“, adjustable gas supply 15-75 W, max. temperature approx. 580 °C



DESCRIPTION

Tool set for the construction and maintenance of networks in the elegant, black nylon zipper case. 23 special tools are placed in nylon pockets and are easy to handle. On the back of the middle wall is a compartment for documents.



Outside: 320 x 250 x 100 mm



without tools: 2000 g
with tools: 2700 g



23 Tools



2700 NETWORK with tool assortment
2701 NETWORK without tool assortment