

## Specifications

- Up to 170MB/s read speed, up to 90MB/s write\*\*
- 4K UHD and Full HD Video<sup>1</sup>
- Class 10, App Performance Class 2 (A2)<sup>2</sup>  
Video Speed Class 30 (V30)<sup>4</sup>,  
UHS Speed Class 3 (U3)<sup>4</sup>
- SanDisk Memory Zone included<sup>3</sup>
- RescuePRO® Deluxe two year  
media recovery software (download offer)<sup>5</sup>
- SD™ adapter included
- Lifetime warranty<sup>6</sup>



Capacities	Performance
<b>64GB-400GB*</b>	<b>C10, U3, V30, A2</b> Up to 170MB/s read; 90MB/s write**
<b>32GB*</b>	<b>C10, U3, V30, A1</b> Up to 100MB/s read; 90MB/s write**




## Set-up information: 32GB, 64GB, 128GB, 256GB, 400GB\*

Product Name	Sales Item No	Single Pack UPC	Master Carton UPC (SCC-14)
32GB SanDisk Extreme PRO® microSDHC™ UHS-I Card with Adapter	SDSQXCG-032G-GN6MA	619659155414 	30619659152391 
64GB SanDisk Extreme PRO® microSDXC™ UHS-I Card with Adapter	SDSQXCY-064G-GN6MA	619659169794 	30619659169795 
128GB SanDisk Extreme PRO® microSDXC™ UHS-I Card with Adapter	SDSQXCY-128G-GN6MA	619659169817 	30619659169818 
256GB SanDisk Extreme PRO® microSDXC™ UHS-I Card with Adapter	SDSQXCZ-256G-GN6MA	619659167837 	30619659167838 

400GB SanDisk Extreme PRO® microSDXC™ UHS-I Card w Adapter	SDSQXCZ-400G-GN6MA	619659167370  6 19659 16737 0	30619659167371  3 06 19659 16737 1
--	--------------------	---	---

## Dimensions – 32GB, 64GB, 128GB, 256GB, 400GB\*

	Weight	Dimension (H x W x L)	Other
<b>Individual Product (card)</b>	0.01 lb 4.54 g	0.43 x 0.59 x 0.04 in 10.92 x 14.99 x 1.02 mm	<ul style="list-style-type: none"> <li>• Master Carton Qty: 5</li> <li>• Languages on Package: English, French, Italian, German, Spanish, Russian</li> <li>• Country of Origin: China or Taiwan</li> <li>• Warranty: Lifetime<sup>6</sup></li> <li>• Has main plug: N/A</li> <li>• Batteries required: N/A</li> <li>• Batteries included: N/A</li> <li>• Battery weight: N/A</li> <li>• Battery material: N/A</li> <li>• Battery capacity: N/A</li> <li>• Battery life: N/A</li> </ul>
<b>Individual Product (adapter)</b>	0.01 lb 4.54 g	1.25 x 0.94 x 0.08 in 31.75 x 23.88 x 2.03 mm	
<b>Packaging Paper</b>	10.4 g		
<b>Packaging Tray</b>	1.60 g		
<b>Total Packaging w/o product</b>	12.0 g		
<b>Single Package</b>	0.03 lb 13.66 g	6.00 x 4.00 x 0.19 in 152.40 x 101.60 x 6.62 mm	
<b>Master Package</b>	0.22 lb 100.39 g	6.3 x 4.49 x 1.22 in 160.00 x 114.00 x 31.00 mm	

- Water Proof<sup>7</sup>
- Temperature Proof<sup>7</sup>
- Shock Proof<sup>7</sup>
- X-Ray Proof<sup>7</sup>



\* 1GB=1,000,000,000 bytes. Actual user storage less

\*\* 64GB-400GB: Up to 170MB/s read speeds, engineered with proprietary technology to reach speeds beyond UHS-I 104MB/s, require compatible devices capable of reaching such speeds. Up to 90MB/s write speeds. Based on internal testing; performance may be lower depending on host device, interface, usage conditions and other factors. 1MB = 1,000,000 bytes.

\*\* 32GB: Up to 100MB/s read; up to 90MB/s write. Based on internal testing; performance may be lower depending on host device. 1MB = 1,000,000 bytes

<sup>1</sup> Compatible device required. 4K UHD (3840x2160) video support may vary based upon host device, file attributes, and other factors. See [www.sandisk.com/HD](http://www.sandisk.com/HD)

<sup>2</sup> Results may vary based on host device, app type and other factors

<sup>3</sup> Download required. See [www.sandisk.com/memoryzone](http://www.sandisk.com/memoryzone)

- <sup>4</sup> Video Speed Class 30 (V30), sustained video capture rate of 30MB/s, and UHS Speed Class 3 (U3) designate a performance option designed to support real-time video recording with UHS enabled host devices. See [www.sdcard.org/consumers/speed](http://www.sdcard.org/consumers/speed)
- <sup>5</sup> Registration required. Terms and conditions apply
- <sup>6</sup> See [www.sandisk.com/wug](http://www.sandisk.com/wug)
- <sup>7</sup> Card only: See [www.sandisk.com/proof](http://www.sandisk.com/proof)

SanDisk, RescuePRO and SanDisk Extreme PRO are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the US and/or other countries. The microSD, microSDHC, microSDXC, SDHC and SDXC marks and logos are trademarks of SD-3C, LLC. Android is a trademark of Google Inc. The Android robot is reproduced or modified from work created and shared by Google and used according to terms described in the Creative Commons 3.0 Attribution License. All other marks are the property of their respective owners.

© 2018 Western Digital Corporation or its affiliates. All rights reserved. Rev. 7/18

Western Digital Technologies, Inc. is the seller of record and licensee in the Americas of SanDisk® products.