

Tool - UNIFOX-C VDE - 1212202

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Combination pliers, cross-notched grip area, integrated M8 - M10 ring wrench, VDE 1000 V AC/1500 V DC tested

Your advantages

- ✔ Ergonomic handle design to eliminate fatigue when working
- ✔ Excellent transformation ratios for excellent gripping and cutting performance
- ✔ Noticeably less force required on the part of the user
- ✔ UNIFOX ... VDE-insulated combination pliers in straight and angled versions

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356454186
Weight per Piece (excluding packing)	264.000 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	180 mm
------------	--------

General

Color	black
Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746
Weight	215 g

Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746

Environmental Product Compliance

Tool - UNIFOX-C VDE - 1212202

Technical data

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 4.0	21040302
eCl@ss 4.1	21040302
eCl@ss 5.0	21040302
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043809
eCl@ss 8.0	21043809
eCl@ss 9.0	21043809

ETIM

ETIM 2.0	EC000142
ETIM 3.0	EC000142
ETIM 4.0	EC000836
ETIM 5.0	EC000836
ETIM 6.0	EC000836

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	23171604

Approvals

Approvals

Approvals


VDE Zeichengenehmigung / EAC / EAC


Ex Approvals


Approval details

Tool - UNIFOX-C VDE - 1212202

Approvals

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	109845
------------------------	---	---	--------

EAC			EAC-Zulassung
-----	---	--	---------------

EAC			RU x- DE.xx08.B.02974
-----	---	--	--------------------------