

## Tool - UNIFOX-P VDE - 1212204

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

### Your advantages

- ✓ The tools feature ergonomic two-component safety handles
- ✓ Individually tested safety tools according to DIN EN 60900 (VDE 0682-201)
- ✓ For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454209
GTIN	4046356454209
Weight per Piece (excluding packing)	200.900 g
Custom tariff number	82032000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	205 mm
------------	--------

#### General

Color	black
Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5745
Weight	205 g

#### Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5745

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

# Tool - UNIFOX-P VDE - 1212204

## Classifications

### eCl@ss

eCl@ss 4.0	21040302
eCl@ss 4.1	21040302
eCl@ss 5.0	21040302
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043816
eCl@ss 8.0	21043817
eCl@ss 9.0	21043816

### ETIM

ETIM 2.0	EC000142
ETIM 3.0	EC000142
ETIM 4.0	EC000833
ETIM 5.0	EC000833

### UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	27112126

## Approvals

### Approvals

#### Approvals

VDE Zeichengenehmigung / EAC

#### Ex Approvals

### Approval details

VDE Zeichengenehmigung		<a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a>	109845
------------------------	--	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--------

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

