

Stripping tool - WIREFOX-E 10 - 1212706

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade


Product Description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212152 WIREFOX 10/SB

Your advantages

- ✓ Flexible, adjustable limit stop for the stripping length
- ✓ Stripping tool with ergonomically shaped pliers.
- ✓ The stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters.
- ✓ Practical integrated wire cutter
- ✓ Flexible, adjustable limit stop for the stripping length
- ✓ Practical integrated wire cutter
- ✓ WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 783613
GTIN	4046356783613
Weight per Piece (excluding packing)	253.000 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	191 mm
Width (a)	20 mm
Height (c)	90 mm
Cable diameter	0.1 mm ... 3.7 mm
Stripping length	18 mm

General

Stripping tool - WIREFOX-E 10 - 1212706

Technical data

General

Color	black/green
Weight	136 g
Min. cross section	0.02 mm ²
Max. cross section	10 mm ²
AWG min	34
AWG max	8

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 4.0	21040302
eCl@ss 4.1	21040302
eCl@ss 5.0	21040302
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043706
eCl@ss 8.0	21043706
eCl@ss 9.0	21043706

ETIM

ETIM 3.0	EC000142
ETIM 4.0	EC000142
ETIM 5.0	EC000168
ETIM 6.0	EC002109

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

EAC

Stripping tool - WIREFOX-E 10 - 1212706

Approvals

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Accessories

Accessories

Knife

Spare knife - WIREFOX 10/SB - 1212152



Replacement blade for WIREFOX 10, for cables and conductors of 0.02 - 10 mm²

Stripping tool

Replacement limit stop - WIREFOX 10/WS - 1200285

Replacement limit stop

Replacement retaining jaw - WIREFOX 10/CJ - 1200286

Replacement clamping jaws for WIREFOX 4, WIREFOX 6SC, and WIREFOX 10
