

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0638190100**
Status: **Active**
Overview: Application Tooling
Description: Hand Crimp Tool for Crimp Terminals

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above. Type: 4D, See Tooling Specification (PDF) Above. Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	<u>Application Tooling</u>
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	800756939599
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 332.600/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents
 ATS-638190100, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(a)-I REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Milli-Grid and MicroBlade Crimp Terminals 24-30 AWG [50394](#) , [50011](#)

Application Tooling Description

FAQ Product #

Milli-Grid Crimp Terminal, Female, 0.38µm Select Gold, Reel, Lead free	503948051
Milli-Grid Crimp Terminal, Female, 0.76µm Select Gold, Reel, Lead free	503948052
Milli-Grid Crimp Terminal, Female, Gold (Au) Flash, Reel, Lead free	503948054
Milli-Grid Crimp Terminal, Female,	503948100

0.38 μ m Select Gold,
Bag, Lead free
Milli-Grid Crimp 503948200
Terminal, Female,
0.76 μ m Select Gold,
Bag, Lead free
Milli-Grid Crimp 503948400
Terminal, Female,
Gold Flash, Bag,
Lead free

This document was generated on 12/21/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION