

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1451350210](#)
Status: **Active**
Overview: Off-the-Shelf (OTS) Discrete Cable Assemblies
Description: Mini-Fit TPA2-to-Mini-Fit TPA2 Off-the-Shelf (OTS) Cable Assembly, Single Row, 1.0m Length, 2 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-----------------------------|--|
| Product Family | Cable Assemblies |
| Series | 145135 |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Mini-Fit TPA2 Both Ends |
| Overmolded | No |
| Overview | <u>Off-the-Shelf (OTS) Discrete Cable Assemblies</u> |
| Product Literature Order No | 987651-6143 |
| Product Name | Mini-Fit TPA2 |
| UPC | 191130113477 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 1.0m |
| Circuits (Loaded) | 2 |
| Color - Resin | Black |
| Gender | Female-Female |
| Lock to Mating Part | Yes |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 34.332/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 4.20mm |
| Plating min - Mating | 2.500µm |
| Plating min - Termination | 2.500µm |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.98-3.14mm |
| Wire Size AWG | 16 |
| Wire/Cable Type | UL 1061 |


Electrical

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 11.0A |
| Voltage - Maximum | 600V AC/DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 4000095324-000 |
|---------------|----------------|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[145135 Series](#)

Mates With

Mini-Fit TPA2 Plug Housing [200471](#) ,
[200488](#)
Mini-Fit Jr. Plug Housing [5559](#)

Mini-Fit Jr. Headers [5566](#) , [5569](#)