

Guitar Tube Amplifier Head - 15W



Description

The Pulse PM15H Guitar Tube Amplifier Head features everything you need for practicing in the bedroom or playing your next gig. 2 separate channels allow you to switch between clean and overdriven tones. Lead switch adds additional gain for blistering solos. The 12AX7 preamp and 6V6 power tubes provide pure tube tone for sparkling cleans, overdriven crunch, or high gain fury. Also features an effects loop, and footswitch input for optional channel switching footswitch (sold separately).

Features


- Output power: 15 Watts
- 2 channels (Clean and Overdrive)
- Lead switch provides extra gain
- Separate Volume control for each channel
- Gain control for Overdrive channel
- 3 band shared EQ (Bass, Middle, Treble)
- 12AX7 preamp and 6V6 power amp tubes
- Effects loop
- Vintage white tolex
- Footswitch input for optional channel switching footswitch (78Y7682 sold separately)

Front Panel



- Input Jack : 1/4" phone jack input.
- Clean : Controls the output level of the clean section.
- Gain : Controls the distortion depth. Turning the knob clockwise increases both distortion and sustain.
- Level : Controls the output level of the drive section.
- Drive Switch : This switches the Drive section between On and Off. When Drive is turned off, the guitar signal inputs through the Clean channel.
- Lead Switch : This switch adds an extra amount of distortion for solo or high gain rhythm playing. Lead switch can only be engaged when the Drive section is On.
- Bass : Controls low frequency range.
- Middle : Controls mid frequency range
- Treble : Controls high frequency range

Rear Panel




- AC Input : Connect the included AC power cable to this connector. Only use this amp with the voltage indicated on the panel.
 - AC Fuse : The fuse is for the AC power. Replace the fuse only with one of the same type and rating.
- Note:** Always disconnect the unit from the power supply before changing the fuse.

Guitar Tube Amplifier Head - 15W

- Speaker Output Jacks : Connect to speaker cabinet with speaker cable. Refer to “Connection to Your Speaker Cabinets”.
- Footswitch Jack 1 : Connect to the footswitch. You can control the Drive and Lead switch via footswitch . When the footswitch is connected , both on/off switches on the front panel are disabled.
- Footswitch Jack 2 : Connect to the footswitch. You can control the reverb effect on and off via footswitch
- Effect Send : This jack provides an output for an external effects unit.
- Effect Return : This jack accepts the output from an external effects unit.

Connecting to Speaker Cabinets

Connecting to speaker cabinets should have been done before turning power on. Speaker Impedance is described at each speaker output jack. Refer to the following figures and ensure the correct connection with your speaker cable.



Only use one speaker output matched to your cabinet.
Damage may occur if more than one cabinets are used.

Part Number Table

Description	Part Number
Guitar Tube Amplifier Head - 15W, 2 Channel, Effects Loop	PM15H