



Prokit's Industries CO., LTD.

5F, No.7, Lane 130,
Ming-Chung Rd., Hsin-Tien Dist,
New Taipei City, Taiwan, R.O.C. Post code: 23114
Tel: 886-2-2218-3233; Fax: 886-2-2218-2722

<http://www.prokits.com.tw> Email: pk-sales@mail.prokits.com.tw

PRODUCT SPECIFICATION

SD-9802

31 IN 1 Precision Electronic Screwdriver Set



*** Picture for reference only. All specifications are subject to change by supplier. ***

Specifications:

	Pieces	N.W. (Kg)	G.W. (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.303	26	13	2.5	-
Inner Box	10	2.59	3.14	27	14	16.5	0.22
CTN	60	18.18	19.54	45	29	34.5	1.59

Bits:


- Torx

The first type symbol	Head Specifications	Size	Surface Finish	Bit Length (mm)	Material
 Torx	T4	4mm	bright	28	S2
 Torx	T5	4mm	bright	28	S2
 Torx	T6	4mm	bright	28	S2
 Torx	T7	4mm	bright	28	S2
 Torx	T8	4mm	bright	28	S2
 Torx	T10	4mm	bright	28	S2
 Torx	T15	4mm	bright	28	S2
 Torx	T20	4mm	bright	28	S2

- specification contents

The first type symbol	Head Specifications	Size	Surface Finish	Bit Length (mm)	Material
 Phillips	PH00	4mm	bright	28	S2
 Phillips	PH0	4mm	bright	28	S2
 Phillips	PH1	4mm	bright	28	S2
 Phillips	PH2	4mm	bright	28	S2
 Slotted	SL1.5mm	4mm	bright	28	S2
 Slotted	SL2.0mm	4mm	bright	28	S2
 Slotted	SL2.5mm	4mm	bright	28	S2
 Slotted	SL3.0mm	4mm	bright	28	S2
 Slotted	SL3.5mm	4mm	bright	28	S2
 Slotted	SL4.0mm	4mm	bright	28	S2


- Communication Bit

The first type symbol	Head Specifications _ communication bit	Hexagonal edge size	Surface Finish	Bit Length (mm)	Material
 Spanner	2.6mm	4mm	bright	28	S2


- content

The first type symbol	Head Specifications	Hexagonal edge size	Surface Finish	Bit Length (mm)	Material
 Triangle	3.0mm	4mm	bright	28	S2

- content

The first type symbol	Head Specifications	Hexagonal edge size	Surface Finish	Bit Length (mm)	Material
 Chevron first batch	3.0mm	4mm	bright	28	S2


- content

The first type symbol	Head Specifications	Hexagonal edge size	Surface Finish	Bit Length (mm)	Material
 Star	2.0mm	4mm	bright	28	S2

- content

The first type symbol	Head Specifications	Hexagonal edge size	Surface Finish	Bit Length (mm)	Material
 Hex	H 0.9	4mm	bright	28	S2
 Hex	H 1.3	4mm	bright	28	S2
 Hex	H 1.5	4mm	bright	28	S2
 Hex	H 2.0	4mm	bright	28	S2
 Hex	H 2.5	4mm	bright	28	S2
 Hex	H 3.0	4mm	bright	28	S2
 Hex	H 4.0	4mm	bright	28	S2

- content

The first type symbol	Head Specifications	Hexagonal edge size	Surface Finish	Bit Length (mm)	Material
 Needle type bits	Needle	4mm	bright	28	S2

	Pieces	N.W. (Kg)	G.W. (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.29	21.2	4.2	3	-
Inner Box	6	1.6	1.7	23	15	20	0.24
CTN	36	9.5	10.5	47	24.5	43	1.75

Individual Packing

- Packing: Double Blister Card

****Remark: Pro'skit Brand****

~ THE END ~