

Braided Sleeving

Product Type:

Braided Sleeving – Retail Pack

Specification:

Polyester expandable sleeving is standard flame-retardant.

It offers durable abrasion resistance in a wide range of industrial applications. The open weave construction allows an easy installation when bundling hoses and cables, even with bulky or large connectors. The expanded the sleeving can reach at least 1.5 times than the initial dimension.

Application:

It mainly used to cover cables, wire harnesses, tubes, industrial hoses where is required a good mechanical protection. Packaged in retail packs (bag and header) or rolls for the 25m lengths.

Standard Colours: Black, Grey

Technology Index

Material: Polyester V-2

Operating Temperature: -50°C-+150°C

Melt point: 240±10°C

Cutting tool: Hot knife



Code	Description	Pack Qty.
ABS6BLKCL	Braided Sleeving 6mm 2 x 1M Pack Black	2 .
ABS6GRYCL	Braided Sleeving 6mm 2 x 1M Pack Grey	2 .
ABS10BLKCL	Braided Sleeving 10mm 2 x 1M Pack Black	2 .
ABS10BLK	Braided Sleeving 10mm 1 x 10M Pack Black	1 .
ABS10GRYCL	Braided Sleeving 10mm 2 x 1M Pack Grey	2 .
ABS10GRY	Braided Sleeving 10mm 1 x 10M Pack Grey	1 .
ABS15BLKCL	Braided Sleeving 15mm 2 x 1M Pack Black	2 .
ABS20BLK	Braided Sleeving 20mm 1 x 10M Pack Black	1 .
ABS15BLK	Braided Sleeving 15mm 1 x 10M Pack Black	1 .
ABS15GRY	Braided Sleeving 15mm 1 x 10M Pack Grey	1 .
ABS20BLKCL	Braided Sleeving 20mm 2 x 1M Pack Black	2 .
ABS20GRYCL	Braided Sleeving 20mm 2 x 1M Pack Grey	2 .
ABS20GRY	Braided Sleeving 20mm 1 x 10M Pack Grey	1 .
ABS20GRY-25	Braided Sleeving 20mm 1 x 25M Pack Grey	1 .
ABS25BLKCL	Braided Sleeving 25mm 2 x 1M Pack Black	2 .
ABS25BLK	Braided Sleeving 25mm 1 x 10M Pack Black	1 .
ABS25GRYCL	Braided Sleeving 25mm 2 x 1M Pack Grey	2 .
ABS25GRY	Braided Sleeving 25mm 1 x 10M Pack Grey	1 .
ABS25GRY-25	Braided Sleeving 25mm 1 x 25M Pack Grey	1 .
ABS30BLKCL	Braided Sleeving 30mm 2 x 1M Pack Black	2 .
ABS30GRYCL	Braided Sleeving 30mm 2 x 1M Pack Grey	2 .
ABS40BLKCL	Braided Sleeving 40mm 2 x 1M Pack Black	2 .
ABS40GRYCL	Braided Sleeving 40mm 2 x 1M Pack Grey	2 .
ABS40GRY	Braided Sleeving 40mm 1 x 10M Pack Grey	1 .
ABS50BLKCL	Braided Sleeving 50mm 2 x 1M Pack Black	2 .
ABS50GRYCL	Braided Sleeving 50mm 2 x 1M Pack Grey	2 .