

6.6 ft. (2 m) DisplayPort 1.4 Cable - VESA Certified

Product ID: DP14MM2M



This DisplayPort 1.4 cable lets you connect your DP laptop or desktop computer to an ultra-high definition 8K monitor, TV or projector.

The DP monitor cable provides the essential final link in your audio-video setups and is ideal for:

- Delivering enriched presentations
- Displaying crisp digital signage walls
- Creating eye-catching visuals for photography, videography, cinematography
- Producing lifelike gaming

VESA® Certified

This DP cable is VESA certified to ensure full compliance and efficient operation of the higher link rate of HBR3. It has been tested to meet all DP 1.4 specifications to ensure quality and reliability.

Experience the Latest That DisplayPort 1.4 Has to Offer

This 8K DisplayPort cable supports all DP 1.4 features:

- Resolutions up to 8K (7680x4320) @ 60Hz, backward compatible with 5K (5120x2880) @ 60Hz and 4K(4096x2160) @ 120Hz and previous generations of DP
- High Bit Rate 3 (HBR3) bandwidths of 32.4Gbps
- High Dynamic Range (HDR) for higher contrast ratio and vivid colors
- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- Display Stream Compression 1.2 (DSC)
- Forward Error Correction
- 32 uncompressed digital audio channels
- HDCP 2.2

Flexible Cable with Latched Connectors

The cable has a thinner 34 AWG construction that allows for flexible installation with minimal clutter, which is perfect for offsite assignments. Each connector features latches that provide secure connections between your devices.

DP14MM2M is backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Deliver enriched presentations using 8K projectors
- Connect to multiple displays on a digital signage wall
- Connect computers to 8K displays: ideal for creative professionals
- Connect a gaming console to an 8K UHD TV

Features

- Deliver high-quality connections with a VESA certified DisplayPort cable
- Experience crisp DisplayPort video with resolutions of up to 8K@60Hz using this 8K DisplayPort cable
- Enjoy higher contrast ratios and vivid colors with HDR support
- Install this flexible 34 AWG DP monitor cable with minimal clutter, or bring it with you for offsite assignments
- Lifetime warranty and guaranteed reliability

Hardware	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	VW-1 Rated
	Number of Conductors	19
Connector(s)	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
Physical Characteristics	Cable Length	2 m [6.6 ft]
	Color	Black
	Connector Style	Latching
	Product Height	10 mm [0.4 in]
	Product Length	2 m [6.6 ft]
	Product Weight	71 g [2.5 oz]
	Product Width	12 mm [0.5 in]
	Wire Gauge	34 AWG
Packaging Information	Shipping (Package) Weight	71 g [2.5 oz]
What's in the Box	Included in Package	1 - DisplayPort Cable

Product appearance and specifications are subject to change without notice.