



CSP604U Professional Surge Protector

Offering home/office environments with computer and communication grade surge protection.

The CyberPower Professional Series CSP604U Surge Protector is ideal for Home/Office protection with 1200 joules, 6 outlets, 2 USB 2.1 Amp charging ports, and a 4 ft. cord. The surge protector is ideal for protecting personal computers, phones/fax/modems, printers, stereos, and other electronics. Its 2.1 Amp USB charging ports are perfect for keeping tablets, smart phones, and other rechargeable electronics ready to use.

The CSP604U features six (6) outlets, MOV technology to guard the surge protector and connected electronics against line abnormalities and lightning surges, while EMI/RFI filters block unwanted line noise.

A Limited Lifetime Warranty ensures that this surge protector has passed our highest quality standards in design, assembly, material or workmanship and further protection is offered by a \$50,000 Connected Equipment Guarantee.

Typical Applications

- Desktop Computers
- Routers & Modems
- Personal Electronics

Features

- 6 Surge Protected Outlets
- 1200 Joules of Surge Protection
- (2) 2.1A USB Charging Ports
- 15A Circuit Breaker
- 4 ft. Cord
- EMI/RFI Noise Filters
- Lifetime Warranty

CSP604U Professional Surge Protector

Offering home/office environments with computer and communication grade surge protection.

GENERAL	
Product Type	Surge Protector
INPUT	
Voltage	125V
Switch	Non Lighted On/Off - Reset
Circuit Breaker	15 Amp
Plug Type	NEMA 5-15P
Plug Style	Right Angle - 45° Offset
Cord Length	4'
OUTPUT	
Outlets - Total	6
Outlet Type	NEMA 5-15R
USB Charge Port - Total	2
USB Charging Amperage	2.1A (shared)
SURGE PROTECTION & FILTERING	
Surge Suppression	1,200 Joules
Maximum Surge Current	60,000 Amps
Maximum Surge Current H-N	30,000 Amps
Maximum Surge Current H-G	15,000 Amps
Maximum Surge Current N-G	15,000 Amps
Clamping Voltage	400V (L-N, L-G, N-G)
Response Time	< 1 nanosecond
EMI/RFI Filtration	150KHz to 100MHz
Attenuation	Up to 32dB
INDICATORS	
Indicators	Protected (Green)
PHYSICAL	
Keyhole Mounting Slots	Yes
CERTIFICATIONS	
Safety	UL1363 / UL1449 3rd Edition, cUL
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	Limited Lifetime
Connected Equipment Guarantee	Lifetime
CEG Amount	\$50,000