

## KTX Professional Woodscrews Technical Specification KTX Gold / Silver / Bronze / Stainless Steel

- KTX head recess
- Suitable for pozi, square, philips square, and KTX screw bits
- Stick fit head for KTX, square and some pozi drive bits. No wobbling or head slippage and minimum damage to head recess from use.
- Yellow passivated (Gold) / BZP (Silver) - Internal, C1022 heat treated hardened steel
- KTX Bronze – Nano coated, C4 rated and salt spray tested over 2200 hours. Inert coating has no reaction with green oak, treated timber or natural occurring chemicals. Made from C1022 heat treated hardened steel. Suited to internal and external use.
- KTX Stainless Steel made from A2 SS302. Suited to internal and external use using construction grade stainless steel.
- Deep drive head recess
- Double countersunk
- Fast pull out capability due to stick fit head
- 4 Angled ribs for smooth finish
- All screws accompanied by 50mm hardened steel KTX bit ideally suited for impact drivers, hammer/drill drivers and drill drivers. All M3.0 use KTX No.1 bit, all M3.5 - M5.0 use KTX No.2 bit and all M6.0 use KTX No.3 bit
- Very sharp start point for fast penetration
- Significantly reduced splitting in timber allowing close to edge fixing
- Lubricated coating for ease of entry into timber
- Suited to hardwood, softwood, MDF, plywood, Chipboard, composite
- Precision TYA-17 curved cut
- Helical thread cut
- KTX Gold Salt spray tested beyond 400 hours
- Coarse thread
- Precision manufactured
- Flat head
- High shear strength for KTX Gold/Silver and Bronze – M3.0 = 3.4KN, M3.5 = 4.1 KN, M4.0 = 5.1KN, M4.5 = 6.2KN , M5.0 = 7.3KN , M6.0 = 10.5KN
- Sizes available M3.0 x 16mm to M6.0 x 200mm
- All KTX screws are CE rated EN:14592

# KTX GOLD WOODSCREWS ( YP ) BOXES / TUBS / BULK CARTONS / CASES / BITS



Item No.	Size	Boxes				Tubs		Bulk Cartons	
		Product Code	Qty	Boxes Per Outer	Outer Qty	Product Code	Qty	Product Code	Qty
1	M3.0 x16	010056	200	80	16,000	010411	2,800	010427	5,000
2	M3.0 x 20	010057	200	80	16,000	010412	2,400	010428	5,000
3	M3.0 x 25	010058	200	50	10,000	010413	2,200	010429	5,000
4	M3.0 x 30	010059	200	50	10,000	010414	2,000	010430	5,000
5	M3.0 x 40	010060	200	24	4,800	010415	1,700	010431	5,000
6	M3.5 x 16	010061	200	80	16,000	010416	2,700	010432	5,000
7	M3.5 x 20	010062	200	80	16,000	010417	2,500	010433	5,000
8	M3.5 x 25	010063	200	50	10,000	010418	2,200	010434	5,000
9	M3.5 x 30	010064	200	50	10,000	010419	1,900	010435	5,000
10	M3.5 x 40	010065	200	24	4,800	010420	1,400	010436	5,000
11	M3.5 x 50	010066	200	20	4,000	010421	1,100	010437	5,000
12	M4.0 x 20	010067	200	50	10,000	010422	2,000	010438	5,000
13	M4.0 x 25	010068	200	50	10,000	010196	1,800	010439	5,000
14	M4.0 x 30	010069	200	50	10,000	010149	1,600	010440	5,000
15	M4.0 x 35	010070	200	24	4,800	010106	1,400	010441	5,000
16	M4.0 x 40	010071	200	24	4,800	010123	1,400	010442	5,000
17	M4.0 x 45	010072	200	20	4,000	010423	1,100	010443	5,000
18	M4.0 x 50	010073	200	20	4,000	010124	1,000	010444	4,000
19	M4.0 x 60	010074	200	20	4,000	010125	900	010445	3,000
20	M4.0 x 70	010075	200	20	4,000	010126	800	010446	2,500
21	M4.5 x 30	010076	200	24	4,800	010424	1,100	010447	5,000
22	M4.5 x 40	010077	200	20	4,000	010193	1,000	010448	5,000
23	M4.5 x 50	010078	200	20	4,000	010127	900	010449	3,500
24	M4.5 x 60	010079	200	15	3,000	010128	700	010450	2,500
25	M4.5 x 70	010080	200	15	3,000	010129	600	010451	2,000
26	M4.5 x 80	010081	200	15	3,000	010130	475	010452	1,500
27	M5.0 x 30	010082	200	24	4,800	010198	1,000	010453	5,000
28	M5.0 x 40	010083	200	20	4,000	010195	900	010454	4,000
29	M5.0 x 50	010084	200	20	4,000	010131	800	010455	3,000
30	M5.0 x 60	010085	200	15	3,000	010132	550	010456	2,000
31	M5.0 x 70	010086	200	15	3,000	010133	500	010457	1,500
32	M5.0 x 80	010087	200	11	2,200	010134	425	010458	1,200
33	M5.0 x 90	010013	150	11	1,650	010135	375	010459	1,200
34	M5.0 x 100	010088	150	11	1,650	010136	325	010460	1,000
35	M5.0 x 120	010089	150	11	1,650	010188	225	010461	800
36	M5.0 x 130	010090	150	11	1,650	N/a	N/a	010462	700
37	M6.0 x 50	010091	200	15	3,000	010425	525	010463	2,000
38	M6.0 x 60	010092	200	15	3,000	010199	450	010464	1,500
39	M6.0 x 70	010093	150	15	2,250	010426	350	010465	1,000
40	M6.0 x 80	010094	150	11	1,650	010187	275	010466	1,000
41	M6.0 x 100	010095	150	11	1,650	010137	250	010467	800
42	M6.0 x 120	010096	100	11	1,100	010052	175	010468	800
43	M6.0 x 130	010097	100	11	1,100	N/a	N/a	010469	700
44	M6.0 x 150	010014	50	10	500	N/a	N/a	010470	700
45	M6.0 x 180	010015	50	10	500	N/a	N/a	010471	700
46	M6.0 x 200	010016	50	10	500	N/a	N/a	010472	500
47	M4.0 x 50 Flooring Screws					010185	800	010473	4,000
48	M4.0 x 55 Flooring Screws					010186	600	010474	3,000

## CASES AND SCREW BITS

	Product Code	Case Qty	
1	Gold Steel Screw Case	010120	1,600
2	KTX Gold Small Plastic Case	010046	700
3	Gold / Silver Steel Case	010122	1,700
4	KTX No.1 Bit - 50mm	010098	N/a
5	KTX No.2 Bit - 25mm	010103	N/a
6	KTX No.2 Bit - 50mm	010099	N/a
7	KTX No 3 Bit - 50mm	010100	N/a
8	Square Drive No.2 Bit - 50mm	010101	N/a
9	Square Drive No.3 Bit - 50mm	010102	N/a

\* All boxes contain 1 x 50mm KTX screw bit suitable for impact and drill drivers

\*\* All tubs contain 2 x 50mm KTX screw bits suitable for impact and drill drivers