

WBB-AFWS61M

Adjustable Fabric Wrist Strap

This wrist strap set features a fully adjustable, stretch elastic wristband and 6 or 12 ft coiled cord. The hypoallergenic, 85 ohm, silver-plated band provides 360 degree conductivity around the wrist for maximum skin contact. OptiSoft band fabric is extra-soft and avoids the scratchy feel of other bands. A machined snap provides a consistent 1 pound removal force. The polyurethane polymer strain reliefs survives 1 million flexes. Cord tangles are reduced by the "spinning style" banana plug. UL Listed. Made in the USA.

Standards

Meets or exceeds the requirements of ANSI/ESD S-1.1, ANSI/ESD S-20.20, EIA 625, MIL-STD-1686, and MIL-HDBK-263. MIL-STD-1686, and MIL-HDBK-263, and EIA 625.

Specifications

Band		Cord	
Fabric:	OptiSoft Elastic Nylon with silver plated threads	Length:	6 or 12 feet, extended
Resistance:	85 ohms typical	Resistor:	1 megohm
Contact:	360 degrees around wrist	Flex life:	1 million flexes
Color:	Light Blue with white edges	Color:	Black
Snap:	4 mm machined post	Markings:	Date Code, resistance
Snap Release:	1 - 5 pounds	Banana Plug:	Spinning, stainless
Markings:	Date Code	Snap:	4mm
Back plate:	Stainless Steel medical grade		


Part Numbers

4mm (1/8") snap

WBB-AFWS	Adjustable Fabric Wristband
WBB-AFWS61M	Adjustable Fabric Wristband and 6 ft cord
WBB-AFWS121M	Adjustable Fabric Wristband and 12 ft cord
CC61M	6 ft cord
CC121M	12 ft cord

10mm (3/8") snap

WBB-AFWS-10	Adjustable Fabric Wristband
WBB-AFWS61M-10	Adjustable Fabric Wristband and 6 ft cord
WBB-AFWS121M-10	Adjustable Fabric Wristband and 12 ft cord
CC61M-10	6 ft cord
CC121M-10	12 ft cord
CC61M-1010	6 ft cord, Stud to Stud
CC121M-1010	12 ft cord, Stud to Stud



Adjustable Fabric Wristband and Cord



P R O D U C T D A T A S H E E T

Wrist Strap - Fabric Band PREMIUM PERFORMANCE

PRODUCT
FABRIC BAND WRIST STRAP

ITEM NUMBER
SEE ABOVE

DATASHEET
1114-A



US and Canada: 866-722-3736
 Fax: 866-722-3735
 Intl: 919-774-3808
 Fax: 919-774-1287
 3010 Lee Avenue Sanford, NC 27330
 email: info@staticcontrol.com
 www.StaticControl.com