

GCS42UW6

2-Port Compact USB VGA KVM with Built-in Cables



The IOGEAR 2-Port Compact USB VGA KVM allows users to share a VGA monitor, USB mouse, and USB keyboard between two computers. It supports multiple operating systems including Windows, Sun, and Mac. Users can switch between computers using a manual switch located on the top of the KVM unit. Being cabled based, users do not have to purchase additional cables in order to use the device. It is entirely plug-n-play and requires no software to run. It is also powered through the USB bus and thus does not require a separate independent power supply to run. It is the perfect KVM for those who want a well-priced, basic KVM that will allow them to multitask with two computers at their disposal. This 2-port KVM also offers a cost effective solution to increase security by allowing users to switch between the Internet connected PC and an Intranet connected PC.

- One USB keyboard, USB mouse, and VGA monitor control two computers
- Separate the Internet and Intranet with the click of a button
- No power adapter required
- Max resolution: 2048 x 1536, DDC2B
- Plug-n-Play monitor support
- Molded-in 4ft cables for simple setup
- Compact design features two attached KVM (USB and VGA) cables
- Compatible with all operation platforms – PC, MAC and SUN
- Supports Windows 2000 or higher, Mac OS 9.0 or higher, Sun Solaris 9 or higher
- No software required – connecting cables to the computers is all it takes
- Computer selection via push buttons
- Full Mac keyboard support
- LEDs allow for easy status monitoring
- 3 Year Limited Warranty



Requirements

-

Console:

- 1 x VGA display
- 1 x standard 104 key wired USB keyboard
- 1 x standard 2 or 3 button wired USB mouse

Computers:

- 1 x VGA port
- 2 x USB ports

Operating Systems:

- Windows® XP, Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
- Mac OS 9 to 10.x
- Oracle® Solaris
- Linux®, Unix and other USB supported systems*

*Additional drivers and support may be needed

drivers and support may be needed

Package Contents

- 1 x 2-Port KVM with cables
- 1 x Quick Start Guide

Specifications

Function	GCS42UW6	Dimensions	GCS42UW6
		POP Information	
		10" Peg Hook	3
		6" Peg Hook	2
		Unit Dimensions	
		Height	0.98in.
		Depth	3.03in.
		Length	3.15in.
		Unit Package Dimensions	
		Width	6.5in.
		Height	9.25in.
		Depth	2.875in.
		Master Carton	
		Width	9.5in.
		Height	7.5in.
		Depth	16.125in.
		Master Carton Qty.	6
		Weight	
		Master Carton Wt.	5.98lb
		Unit Pack Wt.	0.86lb
		Unit Wt. w/accessories	0.64lb
		Unit Wt.	0.64lb