

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0368760002**
Status: **Active**
Overview: Ditto Wire-to-Wire Interconnects
Description: Ditto Hermaphroditic Crimp Terminal, High Copper, Tin Plating, 24-26 AWG

Documents:

Drawing (PDF)	Packaging Specification PK-36876-001-000 (PDF)
Product Specification PS-36876-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-36876-001-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	36876
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Ditto Wire-to-Wire Interconnects
Product Literature Order No	987651-1024
Product Name	Ditto
UPC	887191583358

Physical

Durability (mating cycles max)	25
Gender	Hermaphroditic
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Net Weight	0.148/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50mm
Wire Size AWG	24, 26
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	350V AC/DC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-36876-001-000
Product Specification	PS-36876-001-001, TS-36876-001-001
Sales Drawing	SD-36876-001-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

36876 Series

Use With

Ditto Hermaphroditic Crimp Housing [36877](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Extraction Tool	638131400
Hand Crimp Tool For Ditto Crimp Terminals	638273500
FineAdjust Applicator for Ditto Interconnects Terminals	639030300

This document was generated on 03/15/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION