

PRODUCT DATA SHEET

EVERBUILD® Quick Mac Instant Tarmacadam

HIGH SPECIFICATION TARMACADAM REPAIR COMPOUND

PRODUCT DESCRIPTION

EVERBUILD® Quick Mac Instant Tarmacadam is a high specification Tarmacadam repair compound designed to repair roads, drives and footpaths. May also be used for repairs around roadside ironwork. Ready-to-use cold-lay product, maximum 6mm chip size for permanent compaction, and instantly trafficable.

USES

- Repairing tarmac roads, driveways etc.
- Repairing tarmac footpaths.
- Remedial work around ironworks i.e. drains, man-hole covers etc.

CHARACTERISTICS / ADVANTAGES

- Ready to use cold lay product – just fill and compact down.
- Instantly trafficable
- Will not displace – stays where it is put

PRODUCT INFORMATION

Packaging	25kg tub
Appearance / Colour	Black
Shelf Life	6 months in original unopened bag. This will reduce significantly once opened.
Storage Conditions	Store in cool dry conditions between + 5°C and 25°C. Storage outside these parameters will significantly reduce shelf life.

APPLICATION INSTRUCTIONS

SUBSTRATE QUALITY / PRE-TREATMENT

Correct preparation is the key to maximum durability. Suitable for application where minimum depth is 20mm to 60mm maximum. Compact base with suitable aggregate to required depth below wearing course, and sweep clean of dirt or loose debris. Apply EVERBUILD® COLD JOINT SEALER to any clean-cut ver-

tical surfaces.

APPLICATION

- **High traffic public areas:** (carriageways, footpaths, cycle tracks, tennis courts, etc) For maximum durability a 60mm wearing course is recommended. Apply QUICK MAC into recess and rake to a depth of 45mm (ie 50% greater than compacted depth). Compact to 30mm in accordance with Appendix 8 of the Re-In-

statement of Openings in Highways 1992. Re-seal vertical surfaces with EVERBUILD® COLD JOINT SEALER, re-apply and rake to 45mm, and compact as above back to 30mm level with the existing surface.

- **Low traffic domestic areas:** (eg driveways, garden paths) – prepare, compact base, and prime vertical surfaces in same way as above, but lesser depths of QUICKMAC may be used if required. Holes are filled to 50% greater than their depth and compacted level. NOTE: do not use as a final wearing course at less than 20mm in compacted depth.

LIMITATIONS

- Do not use in a wearing course at less than 20mm depth.
- As the manufacturer cannot know all the uses their products may be put to, it is the users responsibility to determine suitability for use. If in doubt, contact technical services department for advice.

VALUE BASE

All technical data stated in this Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

LOCAL RESTRICTIONS

Note that as a result of specific local regulations the declared data and recommended uses for this product may vary from country to country. Consult the local Product Data Sheet for the exact product data and uses.

ECOLOGY, HEALTH AND SAFETY

Consult MSDS for full list of hazards.

LEGAL NOTES

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

EVERBUILD BUILDING PRODUCTS LTD

Site 41, Knowsthorpe Way
Cross Green Industrial Estate
Leeds, LS9 0SW
Tel: 0113 240 3456
Web: www.everbuild.co.uk
Twitter: @everbuild

SIKA LIMITED

Watchmead
Welwyn Garden City
Hertfordshire, AL7 1BQ
Tel: 01707 394444
Web: www.sika.co.uk
Twitter: @SikaLimited

SIKA IRELAND LIMITED

Ballymun Industrial Estate
Ballymun
Dublin 11, Ireland
Tel: +353 1 862 0709
Web: www.sika.ie
Twitter: @SikaIreland