

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191930184**  
**Status:** **Active**  
**Overview:** VersaKrimp Terminals and Splices  
**Description:** VersaKrimp Ring Tongue Terminal for 8 AWG Wire

**Documents:**

Drawing (PDF) Product Specification PS-19902-013-001 (PDF)  
Product Specification PS-19902-011-001 (PDF) RoHS Certificate of Compliance (PDF)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series 19193  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview VersaKrimp Terminals and Splices  
 Product Name VersaKrimp  
 Type Ring  
 UPC 800755050349

**Physical**

Barrel Type Closed - Brazed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 5.316/g  
 Packaging Type Bag  
 Stud Size 3/8" (M9)  
 Termination Interface: Style Crimp or Compression  
 Wire Size AWG 8

**Material Info**

Engineering Number D-352-38

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19193-036



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

19193 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Manual Putt Pump Hydraulic System, Die set required	<u>192860117</u>
Die Set (large) for the HHLS Hydraulic Crimper	<u>192900001</u>
Hydraulic Dieless Crimping Tool	<u>638161700</u>
Hand Crimp Tool RHT1080 Hand Crimp Tool	<u>640013900</u>
Square "DIN" style dies for 8 AWG	<u>640034400</u>
	<u>640037670</u>

Crimp Head for the 640074400  
AT-200 Pneumatic  
Hand Tool

This document was generated on 03/14/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**