

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002092133**
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket PC Tail Terminal, Series 1376, Male, with Tin/Lead (Sn/Pb) Plated Contact, With Detent, Bag Packaged

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-1190-003 \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------------|--|
| Product Family | Crimp Terminals |
| Series | 1376 |
| Application | Power, Wire-to-Wire |
| Comments | PC Tail For Standard .093" Housing, PC Tail For Standard .093" Housing |
| Crimp Quality Equipment | Yes |
| Overview | Standard .093" Pin and Socket Connectors |
| Product Name | Standard .093" |
| UPC | 800753615410 |

Physical


| | |
|--------------------------------|--------------|
| Gender | Male |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.250/g |
| Packaging Type | Bag |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Termination Interface: Style | Through Hole |
| Wire Insulation Diameter | 4.00mm max. |
| Wire Size AWG | N/A |
| Wire Size mm ² | N/A |

Material Info

Engineering Number 1376-(P909)L

Reference - Drawing Numbers

| | |
|-------------------------|-------------|
| Packaging Specification | PK-1190-003 |
| Product Specification | PS-02-09 |
| Sales Drawing | SD-1376-X |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

1376 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|---|---------------------------|
| Extraction Tool | 11030006 |
| Extractor Tool for .093 and HCS-125 Product Series | 638240200 |