

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0527450797](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 7 Circuits, Gold Plating

Documents:

| | |
|--|---|
| 3D Model | Packaging Specification SPK-52745-002-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-52745-051-001 (PDF) | Product Literature (PDF) |
| Application Specification AS-52745-001-001 (PDF) | Product Literature (PDF) |

Agency Certification

UL E29179

General

| | |
|-----------------------------|---|
| Product Family | FFC/FPC Connectors |
| Series | 52745 |
| Datasheet Order No | 987651-8732, 987651-8736_ZH, 987651-8768_DE, 987651-8772_JA, 987651-8776_KO, 987651-8780_ES |
| Overview | FFC-FPC (SMT) |
| Product Guide Order No | 987651-8061 |
| Product Literature Order No | 987652-0194, Reference Guide# |
| Product Name | Easy-On |
| Series Name | Slider |
| UPC | 822348250455 |

Physical


| | |
|--------------------------------|-----------------------|
| Actuator Type | Slider |
| Circuits (Loaded) | 7 |
| Color - Resin | Black, White |
| Contact Position | Top |
| Durability (mating cycles max) | 20 |
| Flammability | 94V-0 |
| Mated Height | 2.00mm |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Net Weight | 132.148/mg |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PCB Locator | No |
| PCB Mounting | Surface Mount |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 0.50mm |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +85°C |
| Wire/Cable Type | FFC/FPC |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 50V |

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[52745 Series](#)

Application Specification
Packaging Specification
Product Specification
Sales Drawing

AS-52745-001-001
SPK-52745-002-001
PS-52745-051-001
SD-52745-050-001, SD-52745-051

This document was generated on 04/02/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION