

Tel-Splice

Telephone cable splice connectors


Tel-Splice connectors provide an economical and reliable means of splicing telephone cable conductors.

Advantages

- Durable - Highly resistant to moisture and chemical attack.
- Economical - Lower applied cost; IDC, installation displacement connectors, gas tight connections, no pre-stripping required, means minimal operator preparation.
- Versatile - Available in either 2-wire or 3-wire filled version.

Applications

- Load coils
- Stub cables
- Ready access terminals
- Trunk and tool cables.



Product overview

Tel-Splice TSP version

Loose piece description	Sealant	Style	Housing color	Contact material	Max. ID/OD	Part numbers	
						100/box	1000/box
2-wire	Filled	TSP	Blue	Brass	.080"/2.03 mm	737636-2	737636-5

Operating temperature	-25°C to 75°C
Insulation diameter as shown	0.080"/2.03mm
Wire range	19-26 AWG/0.4-0.9 mm
Industry standards	BT listing on Tel-Splice
Technical specifications	108-22040
MSDS for filled product	125-6332

Tel-Splice THG version

Loose piece description	Sealant	Style	Housing color	Contact material	Max. ID/OD	Part numbers
						250/box
3-wire	Filled	THG	Transparent	Brass	.064"/1.63 mm	342816-2

Operating temperature	-25°C to 75°C
Insulation diameter as shown	0.064"/1.63mm
Wire range	19-26 AWG/0.4-0.9 mm
Industry standards	BT listing on Tel-Splice
Technical specifications	108-3050

Hand tool for loose piece applications



Economy hand tool
Part number 790162-1

tyco

Electronics

Tyco Electronics Raychem NV
Diestsesteenweg 692
3010 Kessel-Lo, Belgium
Tel 32-16 351 011 (USA) 1-919-557-8900
Fax 32-16 351 697 (USA) 1-919-557-8498
www.tycoelectronics.com
www.telecomosp.com

a vital part of your world

© 2005 Tyco Electronics
TC 1028/DS/1 04/06

Tyco Electronics Raychem, S.A.
Polígono industrial Mediterráneo
C/. La Fila, parcela 1
46550 Albuixech-Valencia, España
Tel 34-96-141 70 72
Fax 34-96-141 74 15

Tyco is a trademark

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, Tyco Electronics makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. Tyco Electronics' obligations shall only be as set forth in Tyco Electronics' Standard Terms and Conditions of Sale for this product and in no case will Tyco Electronics be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of Tyco Electronics products should make their own evaluation to determine the suitability of each such product for the specific application.