

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0190560010**  
**Status:** **Active**  
**Overview:** VersaKrimp Terminals and Splices  
**Description:** VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire, Non-Insulated, Stud Size 6

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-011-001 (PDF)</a>
<a href="#">Product Specification 194130109-000 (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification 194130110-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR18689
UL	E32244

**General**

Product Family	Ring and Spade Terminals
Series	<u>19056</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>VersaKrimp Terminals and Splices</u>
Product Name	VersaKrimp
Type	Ring
UPC	800755063103

**Physical**

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.454/g
Packaging Type	Carton
Stud Size	6 (M3.5)
Temperature Range - Operating	149°C
Termination Interface: Style	Crimp or Compression
Wire Size AWG	18, 20, 22
Wire Size mm <sup>2</sup>	0.25-1.50

**Material Info**

Engineering Number	A-320-06
--------------------	----------

**Reference - Drawing Numbers**

Product Specification	194130109-000, 194130110-000, PS-19902-011-001, PS-19902-013-001
Sales Drawing	ACD30101



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

19056 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

PremiumGrade Hand	<u>640030100</u>
Crimp Tool	
Crimp Head for the	<u>640070100</u>
AT-200 Pneumatic	
Hand Tool	