

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0934441202

Status:

Active

Overview:

ML-XT Sealed Connection System

Description:

ML-XT Sealed 2 Circuit Receptacle Housing, Pre-Assembled with Large Rear Seal and Cover, Grey



Series image - Reference only

Documents:	
3D Model	Application Specification 934430010-A (PDF)
Drawing (PDF)	Packaging Specification 934430002-K (PDF)
Product Specification 934430010-P (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification STR-1707-001 (PDF)	Product Literature (PDF)

Agency Certification	
UL	E29179
Application tooling part link	
Application Tooling Part Link	63824-5300
General	
Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Overview	ML-XT Sealed Connection System
Product Literature Order No	987651-0201
Product Name	ML-XT
UPC	887191604268
Physical	
Circuits (maximum)	2
Color - Resin	Grey
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.777/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C
Electrical	
Current - Maximum per Contact	13.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P, STR-1707-001
Sales Drawing	934430010-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/88/2018 (15	
January 2019)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93444 Series

Mates With

ML-XT Sealed 2 Circuit Plug Housing

934451202

Use With

ML-XT Male (Pin) Terminal [845240004](#) (Nickel), ML-XT Male (Pin) Terminal [845240014](#) (Selective Gold), ML-XT 2 Circuit Receptacle Wedgelock [93447](#) , ML-XT Blind Cavity Plug [934941000](#)

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Extraction Tool for ML-XT Sealed	638245300

This document was generated on 04/05/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION