


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0471511071](#)
Status: **Active**
Overview: High Definition Multimedia Interface (HDMI)* Products
Description: 0.50mm Pitch HDMI Receptacle, Right-Angle, Front Solder Tab Length 1.80mm, Contact 25µm Gold (Au) Plating, with Back Cover and Mylar, without Upper Flange, Tape and Reel Package, Black Housing, Lead-Free

Documents:

[3D Model](#) [Packaging Specification PK-47151-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-47152-001 \(PDF\)](#)



General

Product Family	I/O Connectors
Series	47151
Application	Wire-to-Board
Component Type	Receptacle
Electrical Model	Yes
Overview	High Definition Multimedia Interface (HDMI)* Products
Product Name	HDMI
Type	N/A
UPC	800756718231

Physical

Boot Color	N/A
Circuits (Loaded)	19
Color - Resin	Black
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Bismuth
Net Weight	2.197/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Panel Mount	Without Flange
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.254µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20° to +85°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	40V DC

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[47151](#) Series

Mates With

[88768](#) HDMI Cable Assembly, [88764](#) HDMI Adapter, [88767](#) HDMI Adapter

Material Info

Reference - Drawing Numbers

Electrical Model Document

Packaging Specification

Product Specification

S-Parameter Model

EE-47151-001, EE-47151-002

PK-47151-001

PS-47152-001

SP-47151-002

This document was generated on 03/28/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION