


Screwdriver set SoftFinish®



assorted 12-pcs.

302 HK12

Order-No.	
41002	1
⊖	4,0 x 100 / 3,5 x 100 / 6,5 x 150
⊕	PH1 x 80 / PH2 x 100 / PH3 x 150
⊗	PZ1 x 80 / PZ2 x 100
⊛	T15 x 80 / T20 x 100 / T25 x 100 / T30 x 115

INFOBOX:  
Wiha SoftFinish®  
screwdriver



The convenient expert for dry applications.


- The SoftFinish handle provides optimal grip for dry applications in trade and industry.
- The position of the soft and hard zones on the handle also supports the perfect grip for quick and powerful turning.

Screwdriver set SoftFinish®




Slotted, Phillips 6-pcs.

302 HK6 SO

Order-No.	
07152	1
⊖	3,5 x 100 / 4,5 x 125 / 5,5 x 150 / 6,5 x 150
⊕	PH1 x 80 / PH2 x 100


Phillips, Pozidriv 6-pcs.

302 HK 601

Order-No.	
26113	1
⊖	4,0 x 100 / 5,5 x 125 / 6,5 x 150
⊕	PH1 x 80 / PH2 x 100
⊗	PZ2 x 100

Slotted, Pozidriv 6-pcs.

302 ZK6 SO

Order-No.	
07153	1
⊖	3,5 x 100 / 4,5 x 125 / 5,5 x 150 / 6,5 x 150
⊗	PZ1 x 80 / PZ2 x 100


TORX® ball end 6-pcs.

362BE K6

Order-No.	
32249	1
⊛	T9 x 60 / T10 x 60 / T15 x 80 / T20 x 80 / T25 x 100 / T30 x 115


TORX® MagicSpring® 6-pcs.

362R K6 SO

Order-No.	
27746	1
⊛	T10 x 80 / T15 x 80 / T20 x 100 / T25 x 100 / T30 x 115 / T40 x 130


TORX® 6-pcs.

362 K6 SO

Order-No.	
07155	1
⊛	T10 x 80 / T15 x 80 / T20 x 100 / T25 x 100 / T30 x 115 / T40 x 130


TORX® 7-pcs.

362 K7

Order-No.	
01299	1
⊛	T8 x 60 / T9 x 60 / T10 x 80 / T15 x 80 / T20 x 100 / T25 x 100 / T30 x 115

TORX® Tamper Resistant (with hole) 6-pcs.

362TR K6

Order-No.	
24506	1
⊛	T10H x 80 / T15H x 80 / T20H x 100 / T25H x 100 / T30H x 115 / T40H x 130