



Einhell

EXPERT PLUS



Cordless Lawn Mower

GE-CM 36/47 HW Li
(2x4,0Ah)

Item No.: 3413160

Ident No.: 11017

Bar Code: 4006825631036

The GE-CM 36/47 HW Li cordless lawn mower is a varied helper in the garden. 3 LEDs show the charge level of the Power-X-Change batteries, which can be used in any of the products from the system series. The brushless motor, the Vortex Technology Deck and central cutting height adjustment deliver exact results. The handle design makes it easy to clean, saves storage space and is height adjustable in three steps. The high wheeler has ball-bearing mounted wheels, features a side ejector function and deflector for ejecting cuttings to the rear, a mulch adapter and a large 75 l grass catch basket and can double the square meters by inserting two additional batteries. Complete with 2 fast chargers, two 4,0 Ah batteries and a cleaning tool.

Features & Benefits

- System battery - Power X-Change battery
- Battery charge level indicator with 3 LEDs
- Batteries can be used for other Power X Change products
- Two system high-speed chargers included
- With a brushless electric motor
- Einhell Vortex Technology Deck
- Central cutting height adjustment, 6 levels
- Einhell handle design including cleaning and storage position
- Folding long handle, height-adjustable with 3 settings & Softgrip
- Catch bag with filling level indicator and 2 emptying handles
- Mulch adapter with mulching function
- Side ejector function/deflector for ejecting cuttings to the rear
- High wheeler including ball-bearing mounted wheels
- Complete with scraper for cleaning in the cleaning position
- Doubling of square meters due to additional battery slots
- Recommended for lawns up to approx. 500 m² (+500 m²)



Technical Data

- Accumulator 18 V (2x) | 4000 mAh | Li-Ion
- Cutting width 47 cm
- Cutting height adjustment 6 settings | 30-65 mm | central
- Capacity of catching device 75 L
- Wheel diameter front 200 mm
- Wheel diameter rear 280 mm

Logistic Data

- Product weight 27.9 kg
- Gross weight single packaging 31.75 kg
- Dimensions single packaging 910 x 600 x 457 mm
- Pieces per export carton 1 Pieces
- Gross weight export carton 31.75 kg
- Dimensions export carton 910 x 600 x 457 mm
- Container quantity (20"/40"/40"HC) 105 | 220 | 220



Available as special accessories



Spare blade GE-CM 36/47 HW Li
Lawn Mower Accessory
Item No.: 3405455
Bar Code: 4006825631050
Einhell Accessory



18V 3,0 Ah Power-X-Change
Battery
Item No.: 4511341
Bar Code: 4006825590593
Einhell Accessory



18V 2,0 Ah Power-X-Change
Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



18V 2,6Ah P-X-C Plus
Battery
Item No.: 4511436
Bar Code: 4006825616590
Einhell Accessory



18V 30min Power-X-Change
PXC-Charger
Item No.: 4512011
Bar Code: 4006825587029
Einhell Accessory



18V 5,2 Ah P-X-C Plus
Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



Power-X-Boostcharger 6 A
PXC-Charger
Item No.: 4512064
Bar Code: 4006825629019
Einhell Accessory



Power-X-Twincharger 3 A
PXC-Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



18V 1,5Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512021
Bar Code: 4006825601350
Einhell Accessory



18V 4,0 Ah Power-X-Change
Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



18V 2,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory



18V 3,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512041
Bar Code: 4006825613698
Einhell Accessory



18V 4,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory