



STENCIL ROLLS

FEATURED PRODUCT

Stencil Rolls

- Used in SMT (surface mount technology) screen printing lines to keep stencil apertures clear of paste residue during the automatic screen printing process
- Prevents smearing, bridging, solder balls, and other problems associated with the stencil printing of solder paste
- Manufactured from a blend of polyester and cellulose fibers
- More paper per roll resulting in less down time, less changeover time, and less inventory required
- Exceptionally low lint levels
- Solvent resistant material results in increased absorption per square inch



Custom Stencil Rolls Available!

Item No.	Machine Type	Core Length	Paper Width	Core ID	Core Type	Paper Length
EB41D1818	DEK	17.87"	17.50"	0.75"	Plastic	39'
EB41D2112	DEK	20.82"	12"	0.75"	Plastic	39'
EB41D2116	DEK	20.82"	15.75"	0.75"	Plastic	39'
EB41D2120	DEK	20.82"	20.25"	0.75"	Plastic	39'
EB41D2121	DEK	21.22"	20.75"	0.75"	Plastic	39'
EB41D2424	DEK	24.37"	24.12"	0.75"	Plastic	39'
EB41E1212	EKRA	11.75"	11.75"	0.50"	Paper	33'
EB41E1616	EKRA	15.75"	15.75"	0.50"	Paper	33'
EB41E2016	EKRA	19.75"	16"	0.50"	Paper	33'
EB41E2020	EKRA	19.75"	19.75"	0.50"	Paper	33'
EB41E2424	EKRA	23.5"	23.50"	0.50"	Paper	33'
EB41F1919	FUJI	19.50"	19.50"	1.0"	Paper	33'
EB41M0909	MPM	9"	9"	0.765"	Paper	55'
EB41M1809	MPM	18"	8.75"	0.765"	Paper	55'
EB41M1812	MPM	18"	12"	0.765"	Paper	55'
EB41M1814	MPM	18"	14"	0.765"	Paper	55'
EB41M1818-1	MPM	18"	17.50"	1.0"	Paper	47'
EB41M1855	MPM	18"	17.50"	0.765"	Paper	55'
EB41M2025	MPM	20.25"	20.25"	0.765"	Paper	55'
EB41M2222	MPM	22"	21.62"	0.765"	Paper	55'
EB41M2424	MPM	24"	23.62"	0.765"	Paper	55'
EB41P1414	PANASONIC	14"	14"	1.5"	Paper	40'
EB41P1414-118	PANASONIC	14"	14"	1.5"	Paper	118'
EB41P1616	PANASONIC	16.12"	16"	1.5"	Paper	40'
EB41P1616-108	PANASONIC	16.12"	16"	1.5"	Paper	108'
EB41P2121	PANASONIC	21.25"	21.25"	1.5"	Paper	40'
EB41P2821	PANASONIC	27.50"	21"	1.5"	Paper	45'
EB41S1616	SMTECH	16"	16"	1.5"	Paper	39'
EB41S2120	SMTECH	20.37"	20.37"	1.5"	Paper	39'
EB41Y1717	YAMAHA	17"	17"	1"	Paper	45'