



Part Number: FL60

Description: Head Lamp

The FL60 Headlamp is one of our newest front loaded headlamps. Equipped with our Wide Angle Flood Beam, this headlamp is perfect for illuminating large areas with its ultra-wide circular beam. A conveniently located button on the front of the headlamp allows the user to swiftly change between high, medium, and low light outputs. The headlamp comes with an IPX4 weatherproof rating and reflective safety strap, making it perfect for any rugged environment you may find yourself.

With Coast's commitment to quality, the FL60 Headlamp is impact resistant, weather resistant and its LED is virtually unbreakable. The FL60 Headlamp is backed by Coast's lifetime warranty against defects in materials and workmanship. Tested and rated to ANSI/FL1 standards.



Specifications:

- **BATTERY LOCATION:** Front
- **BATTERY TYPE:** 3 x AAA (Alkaline)
- **BEAM DISTANCE (HIGH):** 104 ft / 32 m
- **BEAM DISTANCE (LOW):** 39 ft / 12 m
- **BEAM DISTANCE (MEDIUM):** 75 ft / 23 m
- **INCLUDED:** 3 x AAA Batteries | Hardhat Clips | Reflective Safety Strap
- **LIGHT OUTPUT (HIGH):** 400 Lumens
- **LIGHT OUTPUT (LOW):** 55 Lumens
- **LIGHT OUTPUT (MEDIUM):** 305 Lumens
- **RUNTIME (HIGH):** 2 h 45 min
- **RUNTIME (LOW):** 19 h
- **RUNTIME (MEDIUM):** 3 h 30 min
- **WEIGHT:** 3.3 oz / 94 g

Features:



- **HARDHAT COMPATIBLE**

Rugged enough for the outside of the hardhat. COAST headlamps with Hardhat Compatible design include clips for attaching the light to the hat.




- **HIGH|MEDIUM|LOW**

Control your light power with the push of a button. Cycle between full light, medium light and low light options.



- **HINGED BEAM**

Up, down, or straight ahead. All COAST headlamps feature a hinged, tilting head so that you can adjust the light's direction and see right where you're looking




- **REFLECTIVE STRAP**

Stay visible in the dark. Some COAST headlamps feature a Reflective Strap to increase safety and ensure user visibility in low light.



- **WATER RESISTANCE**

Don't worry about the weather. COAST lights that have passed the IPX4-level water resistance test are splash-resistant and built with durable materials that stand up to nature.



- **WIDE ANGLE FLOOD BEAM OPTIC**

See the whole scene at once. The Wide Angle Flood Beam illuminates the broadest possible area with vivid, consistent light from edge to edge. At 6 feet / 1.8 meters distance, the beam shines a clear circle up to 11.5 feet / 3.5 meters in diameter.