

P-touch

P900W / P950NW

brother  
at your side



Warehousing



Logistics



## Professional Network Label Printer Range

Print **durable labels** from your PC, Mac, smartphone or tablet using wireless or wired network connectivity.

- Wired network\* & Wi-Fi to print labels from several devices at once, including tablets/smartphones
- Connect to data contained in spreadsheets to batch print many labels at once
- Software development kits available for Windows, iOS and Android devices
- Range of optional accessories to customise the printer to your needs
- Create durable labels up to 36mm in width
- High speed and high resolution printing
- Advanced cutter with easy label peel function
- Include images, barcodes and frames on your labels

[www.brother.co.uk](http://www.brother.co.uk)



Healthcare



Pharmaceutical



\*PT-P950NW only



*P-touch*

Offering the **highest print speed** and **print resolution** in their class, the **PT-P900** series of **professional label printers** produce durable labels up to 36mm in width. **Print text, barcodes, images and logos onto laminated, durable labels** that are suitable for indoor or outdoor use, and last for many years. Choose from **wireless and wired network connectivity**, and a range of optional accessories to create a **customised label printing solution** that suits your requirements.

### Professional label printers designed for any labelling task

With a wide range of colours combinations and tape widths up to 36mm, near borderless printing and high speed/high resolution print capabilities, these two label printers are ideal for facilities management, document archiving, asset labelling and creating on-demand labels whenever and wherever required.



### Wired and wireless connectivity including Bluetooth

These compact desktop label printers can be connected to your PC or Mac using the integrated USB or Wi-Fi connections. The PT-P950NW can also connect to your wired network thanks to its 10/100 Base-TX network port, and an optional Bluetooth module allows it to easily connect directly to rugged tablets, portable PC's and to Bluetooth input devices such as barcode scanners.

### Industrial label design software for PC and Mac

Both models use the free P-touch Editor label design software for Windows and Mac. It boasts advanced features normally found in expensive desktop applications such as industry standard 1D and 2D barcodes, import of logos and other graphics, and allows you to use the fonts installed on your computer. Link to a Microsoft Excel® spreadsheet or .csv file to print multiple labels quickly and efficiently.



### Print from smartphones or tablets

Instantly create and print simple labels from your smartphone or tablet without needing to start your PC. The Brother iPrint&Label app wirelessly connects to the printer to let you design and print labels from your iOS or Android device. Or if you need to identify electrical and datacom cabling and equipment, use the Brother Cable Label Tool app to print labels for wrapping around cables or for sticking to faceplates, electrical distribution boards and other specialist equipment.



### Wireless connectivity for ultimate flexibility

Create and print labels from your smartphone or tablet quickly without needing to boot your PC or Mac. The Brother iPrint&Label app connects wirelessly using Wi-Fi direct to let you design simple labels on your iOS or Android device.

Or if you need to identify electrical and data cabling and equipment, use the specialised Brother Cable Label Tool app to quickly print labels for wrapping around cables or for sticking to faceplates, electrical distribution boards, cabinets, servers and other equipment. The PT-D800W can also be connected to your office wireless network, and allow multiple users to print labels from their PC or Mac whenever required.



### Include label printing as part of your solution

Software and app developers can use various software development kits for Microsoft Windows, iOS and Android devices to enable label printing from within your own software and apps. This makes these printers ideal to integrate into custom solutions, where durable labels are required.



### Advanced cutter with easy-peel function

The advanced cutter can produce one long strip of labels that are easily peeled one-at-a-time, and ensures your labels are kept in the correct order. Or each label can be fully cut if required.

### Print wherever and whenever required

There are situations where AC power may not be available, such as on construction sites, or if the label printer needs to be used on a portable trolley. Attach the optional battery base and rechargeable lithium-ion battery pack to allow label printing wherever and whenever required.



### Print labels on demand without a PC

Ideal for the food, healthcare and laboratory markets, the optional Touch Panel Display Unit (for PT-P950NW only) lets you print labels without a connection to a PC. Design your label(s) and upload to the required location(s) indicated on the buttons. The user simply then needs to press the relevant button to print that label, on demand. Furthermore, the built-in clock allows labels to include current and future time/date - ideal for "Use By" or "Printed On" labels.

## Optional accessories

PT-P900 takes the serial adapter, battery and battery base only. The PT-P950 takes all the below accessories.



### PA-BB-002

Battery base for li-ion battery



### PA-BT-4000LI

Lithium-Ion rechargeable battery



### PA-SCA-001

RJ25 to DB9M serial adapter



### PA-BI-002

Bluetooth interface (PT-P950NW only)



### PA-TDU-003

Touch Panel display unit for stand-alone printing of labels (PT-P950NW only)

## Specifications

### Label printing

Prints labels up to 36mm in width  
Maximum print height of 32mm for near edge-to-edge printing  
360dpi print resolution for crisp, legible text, images and barcodes  
Fast print speed of 60mm/second  
Built-in automatic label cutter with easy-peel function  
Minimum label length: 4mm | Maximum label length: 1 metre  
Print up to 17 lines per label  
Number of copies: 1-999

#### Connectivity: Wired

USB: Windows®(USB1.1, 2.0, 3.0 protocol) | Mac (USB 1.0, 2.0 protocol)  
Network: 10 Base-T/100 Base-TX (PT-P950NW only)  
Serial: RS-232C (for printing with ESC/P commands only. Requires optional serial adapter)

#### Connectivity: Wireless

Wireless Direct: IEEE802.11n | Ad-Hoc mode: IEEE802.11b | Infrastructure mode: IEEE802.11b/g/n | WPS 2.0

#### Connectivity: Bluetooth (optional accessory for PT-P950NW)

Bluetooth 2.1+EDR | Profiles: SPP, OPP

#### Printer emulations/printer modes

P-touch Raster | ESC/P | P-touch Template

#### Label creation (PC/Mac)

Uses P-touch Editor professional label design software  
Link to data stored in Microsoft® Excel® (Windows®) and .csv (Mac) files, to merge onto your labels  
Choose any of the fonts installed on your PC/Mac to fully customise your label  
Supports popular image formats (.bmp, .dib, .jpg, .tif, .ico, .wmf)  
Special cable labelling wizard to easily create labels for cables, patch panels, faceplates and switches  
Use the date/time stamp to automatically include current or future date/time on your labels

#### Barcode protocols supported:

1D: CODE39, CODE128, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128)  
2D: QR Code, PDF417, Data Matrix, Aztec Code, RSS-14 (Standard, Truncated, Stacked, StackedOmni), RSS-Limited, RSS Expanded (Standard, Stacked)

#### Dimensions and weights

118mm (w) x 192mm (d) x 146mm (h) | 1.48kg (PT-P900W) / 1.51kg (PT-P950NW)

#### Supplied with printer

36mm black on white laminated label cassette (8m)

AC adapter

USB cable

User guide

#### Tape types supported

TZe tape cassettes: 3.5mm-36mm

HSe heat-shrink tube: 5.8mm-23.6mm

FLe die-cut labels: 45mm x 21mm size

## System Requirements

Operating Systems: Microsoft® Windows Vista® | Microsoft® Windows® 7 | Microsoft® Windows® 8 | Microsoft® Windows® 8.1  
Microsoft® Windows® 10 | Microsoft® Windows Server® 2008 | Microsoft® Windows Server® 2008 R2 | Microsoft® Windows Server® 2012  
Microsoft® Windows Server® 2012 R2 | Mac OS X 10.9.5/10.10.x/10.11.x  
Hard disk space: Windows®: More than 70MB | Mac: More than 500MB  
System memory: As per operating system requirements  
Microsoft® Office® support for P-touch add-in:  
Microsoft® Word 2007/2010/2013/2016 | Microsoft® Excel® 2007/2010/2013/2016 | Microsoft® Outlook® 2007/2010/2013/2016

Microsoft, Windows, Windows Server and Windows Vista are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Apple, Mac, Mac OS, iPhone, iPad and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries.

Contact:

## Brother UK Ltd

Shepley Street, Audenshaw, Manchester M34 5JD  
Tel:+44(0)333 777 4444 Fax:+44(0)161 931 2218  
Website: [www.brother.co.uk](http://www.brother.co.uk)