

## SwitchMark SM DIA 60-22 MM GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



### Prevention of incorrect operation: SM

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

### Your benefits with MultiMark

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

### General ordering data

Type	SM DIA 60-22 MM GE
Order No.	<a href="#">2006060000</a>
Version	SwitchMark, Device markers, yellow
GTIN (EAN)	4050118391053
Qty.	450 pc(s).
compatible printer	<a href="#">2430920000</a> <a href="#">2448870000</a>

## Data sheet

### SwitchMark SM DIA 60-22 MM GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	0.1 mm	Depth (inches)	0.004 inch
Net weight	1.133 g	Diameter	60 mm

### General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	yellow	Halogen	No
Material	Polyester	Operating temperature range	-40...120 °C
UL 94 flammability rating	V-0	Version	halogen-free, Self-adhesive

### Device markers

Diameter	60 mm
----------	-------

### Classifications

ETIM 6.0	EC001288	eClass 6.2	27-37-12-25
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

### Approvals

ROHS	Conform
------	---------

### Downloads


Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**SwitchMark  
SM DIA 60-22 MM GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**SwitchMark  
SM DIA 60-22 MM GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**Ink ribbons THM MMP**



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM 76/360 SW	<a href="#">2005080000</a>	Ink ribbon	4050118389951	1 pc(s).

**Accessories / replacement parts**



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
THM MMP ROLLER 115	<a href="#">1357420000</a>		4050118160314	1 pc(s).