

SwitchMark SM 27/18-22 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Prevention of incorrect operation: SM

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

Your benefits with MultiMark

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

Type	SM 27/18-22 MM WS
Order No.	2005840000
Version	SwitchMark, Device markers, 47.75 x 27 mm, white
GTIN (EAN)	4050118391138
Qty.	1,000 pc(s).
compatible printer	2430920000 2448870000

Data sheet

SwitchMark SM 27/18-22 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	27 mm	Width (inches)	1.063 inch
Height	47.75 mm	Height (inches)	1.88 inch
Depth	0.1 mm	Depth (inches)	0.004 inch
Net weight	0.404 g	Diameter	22 mm

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester	Operating temperature range	-40... 120 °C
Size of labelling field	18 x 27 mm	UL 94 flammability rating	V-0
Version	halogen-free, Self-adhesive	Width	27 mm

Device markers

Diameter	22 mm
----------	-------

Classifications

ETIM 6.0	EC001288	eClass 6.2	27-37-12-25
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**SwitchMark
SM 27/18-22 MM WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



**SwitchMark
SM 27/18-22 MM WS**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories

Ink ribbons THM MMP



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM 76/360 SW	2005080000	Ink ribbon	4050118389951	1 pc(s).

Accessories / replacement parts



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
THM MMP ROLLER 115	1357420000		4050118160314	1 pc(s).