

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731130063](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT High-Density D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, 44 Circuits

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------|--------------------------------------|
| Product Family | D-Sub Products |
| Series | 173113 |
| Brochure Order No | 987651-9941 |
| Exclude SD Check | Yes |
| IP Rating | IP20 |
| Overview | FCT D-Sub Connectors |
| Product Category | D-Sub Connector |
| Product Name | FCT Products |
| Type | High Density |
| UPC | 889056324465 |

Physical


| | |
|--------------------------------|------------------|
| Circuits (Loaded) | 44 |
| Circuits (maximum) | 44 |
| Color - Resin | Black |
| Durability (mating cycles max) | 50 |
| Gender | Female |
| Material - Contact | Copper Alloy |
| Material - Resin | PBT |
| Material - Shell | Steel |
| Net Weight | 12.000/g |
| Number of Rows | 3 |
| Orientation | Straight |
| PCB Locator | No |
| PCB Retention | None |
| Packaging Type | Tray |
| Panel Mount | Rear |
| Panel Mount Method | Flange |
| Pitch - Mating Interface | 1.98mm |
| Pitch - Termination Interface | 1.98mm |
| Plating - Contact | Gold over Nickel |
| Plating - Shell | Nickel |
| Polarized to Mating Part | Yes |
| Ports | 1 |
| Shielded | Yes |
| Temperature Range - Operating | -55° to +105°C |
| Termination Style | Solder Cup |
| Waterproof / Dustproof | No |
| Waterproof / Dustproof Type | IP20 |
| Wire Size AWG | 22 |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
|-------------------------------|------|

Material Info

| | |
|--------------------|----------|
| Engineering Number | CT25-44S |
|--------------------|----------|



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[173113 Series](#)

Mates With

FCT High-Density D-Sub, Size 3, 44 Position, Plug

This document was generated on 06/21/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION