

16-Device USB Charging Station Cabinet with Sync for iPad and Android Tablets, Wall-Mount and Cart Options, Black

MODEL NUMBER: **CSC16USB**



Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 16 tablets and other devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSC16USB 16-Device USB Charging Station Cabinet provides fast charging, convenient syncing, secure storage and cord management for up to 16 iPad, Android, Surface and Kindle tablets, as well as mobile phones and other USB devices. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

16 USB ports deliver the fastest charging supported by each device, up to 2.4A per port. A USB uplink port connects to a host computer for wired syncing, though the CSC16USB also supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing).

The cabinet promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering. Flow-through ventilation protects against overheating, the specially coated shelves help prevent scratches and scuffs, and rubber grommets shield cords from damage.

The cabinet also encourages clutter-reducing organization of devices and cabling. Charging cords store out of sight, and a toolless trim panel permits quick service access.

The cabinet is easy to configure. The cabinet ships fully assembled and supports mounting to a wall, desk, table, counter or floor. The front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable dividers accommodate thicker devices. You can also convert it the cabinet to a mobile cart with Tripp Lite's optional CSHANDLEKIT2

Highlights

- Fast 2.4A USB charging and syncing for 16 tablets
- Secures devices in locking, vented steel cabinet with cart option
- Protective shelf with removable dividers and cord management
- Supports mounting to wall, desk, table, counter or floor
- Ships fully assembled for quick, easy installation

Package Includes

- CSC16USB 16-Device USB Charging Station Cabinet, Black
- (2) Keys
- Owner's manual

(sold separately), and roll it where needed.

Features

Fast Charging

- 16 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad, Android, Surface and Kindle tablets
- Also charges mobile phones and other USB devices
- Fits tablets with cases (up to 16.5 x 10.5 x 1.5 in. with cord)
- 10 ft. AC input cord with NEMA 5-15P plug reaches distant outlets

Convenient Syncing

- USB uplink port connects to host computer for wired syncing
- Supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing)

Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- 3-point locking mechanism latches doors at top, middle and bottom
- Built-in hasp and user-supplied padlock can replace or supplement built-in lock
- Rear ports accommodate user-supplied bicycle cable or chain lock
- Flow-through ventilation helps prevent devices from overheating
- Protective shelf specially coated to avoid device scratches and scuffs
- Cord access ports with rubber grommets protect against abrasions
- Solid top work surface helps avoid accidental drips and spills that could damage devices

Clutter-Reducing Organization

- USB ports and charging cords store out of sight
- Shelf includes charging cord access ports for each device
- Toolless trim panel permits quick access to cords

Flexible Configuration

- Ships fully assembled for quick, easy installation
- Supports mounting to wall, desk, table, counter or floor
- Split front doors open 180 degrees for improved device and service access
- Removable dividers accommodate thicker devices like battery chargers
- Firmware upgrade port for future updates
- Converts to mobile cart with optional CSHANDLEKIT2 (sold separately)

Specifications



OVERVIEW	
UPC Code	037332194640
OUTPUT	
Charging Ports / Amps	(16) 2.4A
Charging Method	USB
INPUT	
Voltage Compatibility (VAC)	110; 120
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
PHYSICAL	
Shipping Dimensions (hwd / in.)	24.53 x 33.66 x 23.62
Shipping Dimensions (hwd / cm)	62.31 x 85.50 x 59.99
Shipping Weight (lbs.)	114.00
Shipping Weight (kg)	51.71
Unit Dimensions (hwd / in.)	18.8 x 30.33 x 21.6
Unit Dimensions (hwd / cm)	47.75 x 77.04 x 54.86
Unit Weight (lbs.)	84.66
Unit Weight (kg)	38.40
Color	Black
Slot Dimensions (hwd / in.)	10.6 x 1.5 x 15.4
Slot Dimensions (hwd / mm)	268.1 x 38.2 x 390.5
Charging Station Form Factor	Stationary Cabinet
CERTIFICATIONS	
Certifications	Tested to EIA-310-E, UL60950, FCC & IEC Class B
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>