



Part Number: PDWM12UH

Description: **Wireless Microphone System, Beltpack Transmitter with Headset & Lavalier Mics**

Product Description:

The Pyle Wireless Microphone System, Beltpack Transmitter with Headset & Lavalier Mics - Wireless Headset & Lavalier Microphone System - Simple & Hassle-Free Operation - Reliable, Distortion-Free Performance - Auto Search Syncing with Beltpack Transmitter - LCD Digital Display Screen for Frequency Read-Out - Features 1/4" Jack for Additional Connection - Power ON / OFF Switch - LED Indicator Lights - Battery-Operated Design - Ideal for Karaoke, DJ Sound & House Party Audio - Works with PA System, Amplifier, Mixer, Audio Receiver, etc. - What's in the Box: - Beltpack Transmitter - Receiver Unit - Headset Microphone - Lavalier Microphone.



Features:

- Wireless Headset & Lavalier Microphone System
- Simple & Hassle-Free Operation
- Reliable, Distortion-Free Performance
- Auto Search Syncing with Beltpack Transmitter
- LCD Digital Display Screen for Frequency Read-Out
- Features 1/4" Jack for Additional Connection
- Power ON / OFF Switch
- LED Indicator Lights
- Battery-Operated Design
- Ideal for Karaoke, DJ Sound & House Party Audio
- Works with PA System, Amplifier, Mixer, Audio Receiver, etc.

What's in the Box:

- Beltpack Transmitter
- Receiver Unit
- Headset Microphone
- Lavalier Microphone
- USB Connection Cable
- (2) x 'AA' Batteries
- (2) x 'AAA' Batteries

Technical Specs:

- Microphone System: UHF, PLL 32 Selectable Frequencies
- Wireless Operation Range: Up to 165'+ ft.
- Pickup Pattern: Uni-Directional, Cardioid
- Receiver Interface: 1/4" Audio Connector Jack
- Channel Space: 800kHz
- T.H.D: <0.5%
- Spurious Emission: >40dB
- Maximum Deviation: +/-55Khz
- Audio Dynamic Range: >100dB
- S/N Ratio: >96dB @ 1kHz, A-Weighted
- Battery Operated Beltpack, Requires (2) 'AA' Batteries
- Battery Operated Receiver, Requires (2) 'AAA' Batteries
- *Receiver Can Also be Powered via USB Cable
- Beltpack Dimensions (L x W x H): 4.3" x 2.5" x 0.8" -inches
- Receiver Dimensions (L x W x H): 3.4" x 2.4" x 0.7" -inches
- Sold as: 1
- Weight: 1.15 lbs.