

# 0.8 m (2.7 ft.) Thunderbolt 3 to Thunderbolt 3 Cable - 40Gbps

Product ID: TBLT34MM80CM



This Thunderbolt 3 to Thunderbolt 3 cable lets you deliver video, data and power to your Thunderbolt 3, USB 3.2 and DisplayPort devices. At 0.8 meters in length, the Thunderbolt cable provides added flexibility and distance when connected to your devices.

## USB-C Compatibility

Fully compatible with your USB 3.2 Gen 2 devices, this cable can be used for charging and syncing your mobile devices. Also, connect and power USB-C laptops, such as your MacBook or Chromebook, and USB-C peripherals, such as your docking station.

## Unbelievable Data Transfer Speeds

This Thunderbolt 3 USB-C cable supports data transfer rates up to 40Gbps when connected to a Thunderbolt 3 device, enabling lightning fast performance. When connected to a USB 3.2 device, this cable supports rates of 20Gbps.

## **Enjoy Ultra High Definition Video**

This cable supports dual 4K 60Hz or full 5K 60Hz video for an astonishing resolution, contrast, and color depth.

## **Versatile Power Delivery**

The Thunderbolt 3 Type-C cable delivers up to 100W of power for charging a Thunderbolt 3 laptop, which means you can keep your devices powered without using an additional power supply.

## **Enable Thunderbolt Networking**

Bridge multiple Thunderbolt 3 USB-C enabled laptops for peer-to-peer 10GbE networking with this cable. It's also perfect for sharing peripherals such as printers and storage.

TBLT34MM80CM is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Features

- Thunderbolt certified cable delivers full Thunderbolt 3 performance and compatibility
- Experience unbelievable data transfer rates of up to 40Gbps when connected to Thunderbolt 3 devices
- Enjoy astonishing resolution by connecting to either a 5K display or two 4K UHD monitors
- Supports single-cable docking while powering and charging your laptop at the same time
- Easily set up peer-to-peer networking with multiple Thunderbolt 3 laptops

<b>Hardware</b>	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Performance</b>	Type and Rate	Thunderbolt 3 - 40 Gbit/s
<b>Connector(s)</b>	Connector A	1 - Thunderbolt™ 3 USB-C (24-pin) (40Gbps) Male
	Connector B	1 - Thunderbolt™ 3 USB-C (24-pin) (40Gbps) Male
<b>Physical Characteristics</b>	Cable Length	2.6 ft [0.8 m]
	Color	Black
	Product Height	0.3 in [0.6 cm]
	Product Length	2.6 ft [0.8 m]
	Product Width	0.5 in [12.3 mm]
	Weight of Product	1.2 oz [35 g]
<b>Packaging Information</b>	Package Height	0.4 in [10 mm]
	Package Length	5 in [12.7 cm]
	Package Width	8.6 in [21.9 cm]
	Shipping (Package) Weight	0.1 lb [0 kg]
<b>What's in the Box</b>	Included in Package	1 - 0.8 m Thunderbolt 3 Cable

Product appearance and specifications are subject to change without notice.