


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2068321201](#)  
**Status:** **Active**  
**Overview:** [Micro-Fit Connector System](#)  
**Description:** Micro-Fit+ Vertical Header, 3.00mm Pitch, Dual Row, 12 Circuits, Tin over Nickel Plating, UL 94V-0, Glow-Wire Capable, Black

**Documents:**

[Drawing \(PDF\)](#) [Test Summary 2064600000-TS-000 \(PDF\)](#)  
[Product Specification 2064600000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 2068320000-PK-000 \(PDF\)](#)



**General**

Product Family	PCB Headers
Series	<a href="#">206832</a>
Application	Power, Wire-to-Board
CURRENT-MAX-NUMERIC	12.5
Datasheet Order No	987651-9552
Overview	<a href="#">Micro-Fit Connector System</a>
PITCH-MATING-NUMERIC	3.00
Product Name	Micro-Fit+
UPC	191130125258

**Physical**

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	25
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin over Nickel
Material - Resin	Liquid Crystal Polymer
Net Weight	1.496/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.18mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	12.5A
Voltage - Maximum	600V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2068320000-PK-000
Product Specification	2064600000-PS-000
Sales Drawing	2068320000-SD-000
Test Summary	2064600000-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[206832](#) Series

**Mates With**

Micro-Fit+ Receptacle [206461](#)

This document was generated on 06/07/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**