

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0751170118**  
**Status:** **Active**  
**Overview:** VHDM Backplane Connector Systems  
**Description:** VHDM Single-Ended Board-to-Board Stacker Receptacle, 18mm Stack Height, 2.00mm Pitch, Vertical, 8 Rows, 80 Circuits, 0.76µm Gold (Au)

**Documents:**

[3D Model](#) [Packaging Specification PK-70873-0750 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**


Product Family	Backplane Connectors
Series	75117
Application	Board-to-Board Mezzanine
Application Tooling Documents	TM-622010999
Comments	Stack Height 18.00mm, Lead-Free, Stack Height 18.00mm, Lead-Free
Component Type	PCB Receptacle
Overview	VHDM Backplane Connector Systems
Product Name	VHDM
UPC	756054905852

**Physical**

Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	Copper-Nickel-Silicon, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	13.060/g
Number of Columns	10
Number of Pairs	Open Pin Field
Number of Rows	8
Orientation	Vertical
PC Tail Length	2.85mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.80mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

**Electrical**

Current - Maximum per Contact	3.0A
Data Rate	3.125 Gbps
Voltage - Maximum	120V AC (RMS)/DC



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

75117 Series

**Mates With**

74060 VHDM Board-to-Board Backplane Header

**Solder Process Data**

Lead-freeProcess Capability

N/A

**Material Info****Reference - Drawing Numbers**

Packaging Specification

PK-70873-0750

Sales Drawing

SD-75117-001

This document was generated on 07/03/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**