



Technical Specification

Material:	PE(LDPE and LLDPE) film
Product Height:	50-90 microns
Surface Finish:	Smooth
Operating Temperature:	60°C 160 hours
Country of Origin:	Taiwan
Storage and Application:	The product should be protected against direct sunlight and extremes in temperature and humidity and stored upright in its original packaging. The film should be applied within a 3 month period from the delivery date. The film should be removed within 30 days from the date of lamination. Surface preparation is important. The substrate should be clean and free from residue, such as dust and oil, when the tape is applied in order to achieve optimum adhesion. Do not press too hard when applying. This may cause the end of the tape to peel. If applying to surfaces treated with machining oil, degrease the surface carefully. Any remains will be a cause for surface contamination or adhesive residue
Adhesion Strength:	1,000-2,000 g/50mm
Tensile Strength:	≥45 N/mm
Elongation:	≥300%
Application Temperature:	Cold can affect the peel strength. Please apply the film at room temperature (10°C to 30°C)

COBAGuard

Self-adhesive floor protection film - hard floor and carpet options

- Does not feature COBA Guard logo as standard, however can be branded with your logo. Call for details.
- Self-adhesive polyethylene protection film.
- Ideal floor protection for maintenance, show houses etc.
- Film is reverse wound on the roll for rapid installation.
- Install by hand for smaller rooms/ staircases or use applicator for larger areas.
- Does not leave marks or residues.
- Flame retardant to BS4790:1987.

Sizes	Hard Floor	Carpet	Weight
0.6m x 25m	CGH00001	CGC00001	1.50 kg
1.2m x 25m	CGH00002	CGC00002	2.00 kg
0.6m x 50m	CGH00003	CGC00003	2.00 kg
1.2m x 50m	CGH00004	CGC00004	6.00 kg
0.6m x 100m	CGH00005	CGC00005	4.00 kg
1.2m x 100m	CGH00006	CGC00006	8.00 kg



Technical Specification

Material:	PE(LDPE and LLDPE) film
Surface Finish:	Smooth
Product Height:	80 microns
Operating Temperature:	60°C 160 hours
Typical Applications:	The film can be applied to most surfaces including carpet, laminate, ceramics and glass
Flame Retardancy:	No Flaming
Country of Origin:	Canada
Application Temperature:	Cold can affect the peel strength. Please apply the film at room temperature (10°C to 30°C)

COBAGuard Universal

Protects floor surfaces from paint and debris when decorating

- Can be used on both carpet and hard floors.
- The film can be applied to most surfaces including carpet, laminate, ceramics and glass.

Size	Part Code	Weight
0.6m x 10m	CGU00001	1.00 kg