

## PRODUCT DATA SHEET

# EVERBUILD STICK2<sup>®</sup> Carpet Fix Spray

HIGH TACK SPRAY ADHESIVE, IDEAL FOR LAYING CARPETS

## PRODUCT DESCRIPTION

EVERBUILD STICK2<sup>®</sup> Carpet Fix Spray is a sprayable high tack adhesive that fixes P.U and foam backed carpets, carpet tiles, underlay, paper felt and cork to most common substrates.

## USES

- Fixing most common types of PU and foam backed carpets to most common surfaces.
- Fixing carpet tiles.
- Bonding metals to most surfaces.
- Bonds rubber, most plastics and leather
- As a general purpose household/hobby adhesive

## CHARACTERISTICS / ADVANTAGES

- Good adhesion - fast rate of tack development.
- Ease of use - no messy spreading/clean up.
- Time saving- easier and quicker than most trowel/spreader applied adhesives.
- Foaming formula - gives low soak in into most substrates.
- Halogen and CFC Free.
- Repositionable.

## PRODUCT INFORMATION

<b>Chemical Base</b>	Synthetic rubber/resin.
<b>Packaging</b>	500ml Aerosol Can
<b>Colour</b>	Yellow / Amber
<b>Shelf Life</b>	12 months from date of manufacture in original unopened containers.
<b>Storage Conditions</b>	Store in original unopened containers between 5 and 25°C. Store as flammable liquid.

<b>Solids</b>	10 - 20%
<b>Coverage</b>	~ 2.5 m <sup>2</sup> for 500ml can
<b>Tack Life</b>	2 - 5 minutes
<b>Flash Point</b>	-40°C
<b>Cleaner</b>	Everbuild Gun Foam Cleaner

## APPLICATION INSTRUCTIONS

### SUBSTRATE PREPARATION

The surfaces to be glued should be clean and free from dust, grease and other contaminants. Materials should be stored in a warm environment prior to bonding to avoid chilling of the glue line, which leads to extended setting times.

### APPLICATION METHOD / TOOLS

Shake the can well before use.

Select the fan width by turning the nozzle to the desired position. Spray adhesive from 6-8 inches (15 to 20 cm approx.) away onto one or both surfaces; depending on the type of surface/strength of bond required.

#### **STRONG BONDING:**

Apply 1-3 coats (depending on strength required) to both surfaces. Allow solvent to evaporate (30 seconds) and press surfaces together from centre outwards.

#### **TEMPORARY REPOSITIONABLE BONDING:**

Spray on one surface only and allow to dry for 2-3 minutes before bonding. Excess adhesive can be removed with STICK 2 CONTACT ADHESIVE THINNER AND CLEANER or EVERBUILD GUN FOAM CLEANER. To prevent spray nozzle from blocking, at the end of each use, turn can upside down and press nozzle until spray is clear of adhesive.

The newly bonded materials should not be subjected to extreme temperature changes for 3 to 4 days after bonding. Avoid further fabrication until the adhesive has fully dried.

### LIMITATIONS

- Do not use to fix vinyl floor tiles.
- Do not use on polystyrene. Use EVERBUILD GUN A NAIL
- Do not use on cellulose painted surfaces
- Do not use on bitumen or tar leaching products.
- Medium strength adhesive, do not use on heavily trafficked/industrial areas.

## VALUE BASE

All technical data stated in this Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

## LOCAL RESTRICTIONS

Note that as a result of specific local regulations the declared data and recommended uses for this product may vary from country to country. Consult the local Product Data Sheet for the exact product data and uses.

## ECOLOGY, HEALTH AND SAFETY

For information and advice on the safe handling, storage and disposal of chemical products, users shall refer to the most recent Safety Data Sheet (SDS) containing physical, ecological, toxicological and other safety-related data.

## LEGAL NOTES

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

#### EVERBUILD BUILDING PRODUCTS LTD

Site 41, Knowsthorpe Way  
Cross Green Industrial Estate  
Leeds, LS9 0SW  
Tel: 0113 240 3456  
Web: [www.everbuild.co.uk](http://www.everbuild.co.uk)  
Twitter: @everbuild

#### SIKA LIMITED

Watchmead  
Welwyn Garden City  
Hertfordshire, AL7 1BQ  
Tel: 01707 394444  
Web: [www.sika.co.uk](http://www.sika.co.uk)  
Twitter: @SikaLimited

#### SIKA IRELAND LIMITED

Ballymun Industrial Estate  
Ballymun  
Dublin 11, Ireland  
Tel: +353 1 862 0709  
Web: [www.sika.ie](http://www.sika.ie)  
Twitter: @Sikalreland

EVERBUILDSTICK2CarpetFixSpray-en-GBEVER-(03-2018)-1-1.pdf