INDUSTRIAL - ENVIRONMENTALLY SEALED SWITCHES

Series - 8510, 8511, 8512

Environmentally Sealed Toggle Switches

FEATURES				CU	RRE	NT RA	TINGS			
 Completely sealed against dust, moisture, and other contaminants 	 See 8520-8528 for UL recognized and CSA certified version on page 5 	No. of Poles	Catalog Number	Type of Operation	28VDC			115 VAC 60 or 400Hz		
 1, 2 and 4 pole circuitry One hole mounting for easy installation 	 Water tight seal per MIL-STD-108E and designed to meet IP68 Thermoset molding materials meet 				Lamp Load	Resistive Load	Inductive Load	Lamp Load	Resistive Load	Inductive Load
 Multi-circuits offered 2 & 3 position with maintained and momentary action Molded-in terminal inserts Molded-in terminal numbers 	flame retardant requirements Temperature Range: -50°F to +150°F (-46°C to +66°C) Life: 20,000 operations at rated load Bushing: 15/32" - 32 thread	1	8510	Maintained Momentary	5 4	20 15	15 10	3 2	15 15	10 7
		2	8511	Maintained Momentary	7 5	20 18	15 10	4 2	15 11	15 8
		4	8512	Maintained	5	20	12	4	15	15
SELECTION TABLE				Momentary	4	18	10	2	11	8

FLUSH TERMINAL SCREWS







CIRCUIT WITH LEVER IN		ONE POLE	TWO POLE	FOUR POLE		
Up Position	Center Position	Down Position (Keyway)				
7	1	▲	Catalog Number	Catalog Number	Catalog Number	
ON	OFF	ON	8510K1	8511K1	8512K1	
ON	NONE	OFF	K9	K9	K9	
ON	NONE	ON	K4	K4	K4	
ON	OFF	NONE	K6	K6	K6	
ON	NONE	ON*	8510K5	8511K5	8512K5	
* ON	OFF	ON*	K2	K2	K2	
NONE	OFF	ON*	K7	K7	K7	
ON	NONE	OFF*	K10	K10	K10	
OFF	NONE	ON*	K11	K11	K11	
ON	OFF	ON*	8510K3	8511K3	8512K3	
* ON	ON	NONE	K12	K12	K12	
ON	ON	NONE	K13	K13	K13	
ON	ON	ON	_	8511K14	8512K15	
ON	ON	ON*	_	K15	K16	
* ON	ON	ON*	_	K16	K17	
ON	ON	ON	_	8511K17	_	
ON	ON	ON*	_	K18	_	
* ON	ON	ON*	_	K19	_	
ON	ON/OFF	ON	_	_	8512K20	

* Momentary contact. See Page A71 for circuit diagrams.







INDUSTRIAL - ENVIRONMENTALLY SEALED SWITCHES Environmentally Sealed Toggle Switches

Series - 8510, 8511, 8512

MOUNTING DIMENSIONS - ONE POLE / 8510






Mounting dimensions for reference only.

Non-functional terminals not supplied.



INDUSTRIAL - ENVIRONMENTALLY SEALED SWITCHES Series - 8510, 8511, 8512

Environmentally Sealed Toggle Switches




Terminal Identification


OPTIONS/ACCESSORIES

PANEL CUTOUT DIMENSIONS

- Special mounting hardware
- Mounting hardware furnished assembled
- Terminal screws furnished assembled
- Special toggle levers
- Special circuits
- Panel seal, Part Number 32-341
- Spade terminal adapters available

15/32 DIA. BUSHING





STANDARD 0.00 = inches[0,0] = mm

Mounting dimensions for reference only.

Non-functional terminals not supplied.

SAFRAN ELECTRICAL & POWER

