Kasa Smart Light Bulb

Multicolor

KL130B

Remote Control | Scheduling | No Hub Required | Voice Control

Highlights

Multicolor

With a wide range of colors and adjustable brightness, the Kasa bulb offers endless lighting possibilities to fit any environment and mood. You can choose a light for everything from a dinner party to a late-night study session.

Multi-scene

Create multiple scenes like theater scene, party scene or sleeping scene with different settings for various occasions, and tap yours when you want the light your way.

works with the Google Assistant

WORKS WITH amazon alexa

Works with Microsoft Cortana

Highlights

Schedules

Use your Kasa Smart app to schedule your light bulb to automatically switch on and off when you're home or away.

Your Home. One App.

With the Kasa Smart app, you can easily access and control smart plugs, cameras, light switches, bulbs and more. Checking in on your home is only a few taps away.

Cameras

Bulbs

Light Switches

Plugs

Learn more at tp-link.com/smarthome

Features

Ease of Use

· No Hub Required – Connect to your existing Wi-Fi router with no extra hub required

· Remote Control – Control your smart bulbs from anywhere with the free Kasa app

· Scheduling – Set schedules to turn on/off the smart bulbs at any chosen time for your convenience

· Multi-scene – Save your light settings as different scenes to enjoy instant access to them

· Auto White – Set your bulb to automatically adjust its color temperature to match natural light patterns from dawn to dusk

Compatibility

· Works with Vocie Assistants – Control smart bulbs using the leading voice assistants such as Amazon Alexa, Google Assistant and Microsoft Cortana

· Works with IFTTT – Set interactions between a wide array of devices, software, and services using IFTTT

· Compatible with Android, iOS – The free Kasa app lets you run smart bulbs from any Android (4.4 and higher) or iOS (iOS 10 and higher) devices.

Lighting

· Multicolor – Choose a different color for any occasion.

· Durable Bulb – Provide you stable and customized lighting for up to 22.8 years**

*60W equivalent

**Based on 3hrs/day

Specifications

Working Status

· Typical Lumen Output: 800lm

· Input Power (Actual power draw in Watts): 10W

· Color Temperature: 2500K ~ 9000K (adjustable via app and cloud)

· Rated Input Voltage: 220 -240V 50/60Hz

· Beam Angle: 230 Degrees typical

· Dimmable: Yes (via app and cloud only)

· Tunable: Yes (via app and cloud only)

· Color Changing: Yes (via app and cloud only)

Network

· Secured home Wi-Fi connection required

· Wi-Fi Protocol: IEEE 802.11b/g/n

· Wi-Fi Frequency: 2.4GHz

· System Requirements: Android 4.4 or higher, iOS 10 or higher

General

· Package Contents:

  Kasa Smart Light Bulb

  Quick Start Guide

· Lamp Base: A60 bulb, B22 fitting

· Weight: 0.304 lb (0.138kg)

· Dimensions: 2.36 x 4.76 in (60 x 121 mm)

· Certifications: CE, RoHS, SAA, RCM

· Operating Temperature: -15 ºC~ 40 ºC (5°F ~ 104°F)

· Operating Humidity: 10%~90%RH, Non-condensing

www.tp-link.com