


81 series keyfobs



Product overview

Small ABS handheld enclosures, for wireless remote control and RFID type products.

- Tactile handheld fob box
- Snaps together without the need for screws
- Ergonomic design
- Comfortable shape
- Holes for strap or lanyard
- Colours available, white and black as standard, blue, green and pink upon request
- PCB pillars
- 81 series has been designed to meet the requirements of IP40



SPECIFICATION	
Material	Base and lid ABS UL94-HB
Operating temperature	-10°C to +60°C
Standard colours	Black or white
Protection class	81 series has been designed to meet the requirements of IP40
Standard unit includes	Base and lid

PART NO.	LENGTH	WIDTH	HEIGHT	COLOUR	STYLE
CHH81E1WH	65mm	35mm	11mm	White	Pebble
CHH81E1BK	65mm	35mm	11mm	Black	Pebble
CHH81E2WH	85mm	48mm	15mm	White	Pebble
CHH81E2BK	85mm	48mm	15mm	Black	Pebble
CHH81E3WH	50mm	50mm	14mm	White	Round
CHH81E3BK	50mm	50mm	14mm	Black	Round
CHH81E4WH	100mm	58mm	18mm	White	Pebble
CHH81E4BK	100mm	58mm	18mm	Black	Pebble

Wrist straps

- Wrist straps for 81 series slim plastic enclosure, available in six colours pink, yellow, green, blue, grey and black.



PINK	YELLOW	GREEN	BLUE	LIGHT GREY	BLACK	LENGTH	WIDTH
CHHWRSTPK	CHHWRSTYL	CHHWRSTGR	CHHWRSTBL	CHHWRSTLG	CHHWRSTBK	140mm	8mm

Neck straps

- Neck straps for the slim plastic enclosure, available in six colours.
- Neck strap comes with quick release joint



PINK	YELLOW	GREEN	BLUE	LIGHT GREY	BLACK	LENGTH	WIDTH
CHHNECKPK	CHHNECKYL	CHHNECKGR	CHHNECKBL	CHHNECKLG	CHHNECKBK	450mm	10mm

KEY FEATURES

Ergonomic design | Snap-in assembly | PCB pillars



292
UNIVERSAL ENCLOSURES

318
HEAVY DUTY AND ELECTRICAL ENCLOSURES

342
DESKTOP AND INSTRUMENT CASES

348
DEVELOPMENT BOARD ENCLOSURES

367
ROOM SENSOR ENCLOSURES

370
CUSTOM SIZED ENCLOSURES

PLASTIC ENCLOSURES

