

Warning label - US-PML-W100 (100X100) - 1014127

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Warning label, Card, yellow/black, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 100 x 100 mm, Number of individual labels: 1




Your advantages

- UniSheet - stick-on warning labels, unmarked
- Suitable for indoor and outdoor use
- The warning labels conform to the ISO 7010 international standard
- Highly flexible, plasticized PVC labels which are ideal for uneven surfaces



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 786409
GTIN	4046356786409
Weight per Piece (excluding packing)	5.990 g
Custom tariff number	39199080
Country of origin	Germany

Technical data

Dimensions

Length (b)	100 mm
Width (a)	100 mm
Height (c)	86.8 mm
Diameter	0.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------

General

Warning label - US-PML-W100 (100X100) - 1014127

Technical data

General

Color	yellow/black
Type	Triangle
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Environmental Product Compliance

	Reaction mass of DOTE and MOTE
--	--------------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27371300
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC001777
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718

Warning label - US-PML-W100 (100X100) - 1014127

Classifications

UNSPSC

UNSPSC 20.0	55121718
UNSPSC 21.0	55121718

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards